

# Levity® Frameless Sliding Shower Door K-706165-L

#### Features

- Frameless design emphasizes glass and creates a sleek, minimalist look.
- Frameless, 5/16" (8 mm) thick Crystal Clear tempered glass door.
- Innovative roller design simplifies installation and provides out-of-plumb adjustability.
- Door tracking system features a hidden, cushioned, center guide for smooth, quiet sliding action.
- Smooth, easy-to-clean wall jambs.
- Vertical blade handles accentuate the contemporary style.
- CleanCoat<sup>®</sup> technology creates a barrier between the water and glass to help keep your shower door looking new.

#### Material

- Anodized aluminum hardware prevents rusting or corrosion.
- Tempered glass ensures maximum safety and durability.

#### Installation

- Out-of-plumb adjustability allows for simpler installation.
- Can be installed to open to the left or right.

# Components

Product includes:

- 706265-L
- 706365-L
- Additional included component/s: Hardware Kit.



# Codes/Standards

ANSI Z97.1 (Tempered Glass) CPSC 16CFR 1201

# **KOHLER® One-Year Limited Warranty**

See website for detailed warranty information.

# **Available Color/Finishes**

Color tiles intended for reference only.

#### Color Code Description



SHP Bright Polished Silver

- NX Brushed Nickel
- ABZ Anodized Dark Bronze


#### Available Glass Options Code Description

Crystal Clear





Levity® Frameless Sliding Shower Door K-706165-L



# **Technical Information**

All product dimensions are nominal.

Installation type:For shower base installationOpening style:Sliding/BypassOpening Width - Min:56-5/8" (1438 mm)Opening Width - Max:59-5/8" (1514 mm)Walk-through - Min:24-9/16" (624 mm)Walk-through - Max:27-9/16" (700 mm)Glass thickness:5/16" (8 mm)Glass coating:CleanCoat®

#### Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 84-1/2" (2146 mm) to allow for installation clearance.

