

Memoirs® Classic

Comfort Height® Toilet K-6424

Features

- Vitreous china.
- One-piece.
- Comfort Height® Compact elongated bowl.
- AquaPiston® flushing system.
- Includes left-hand polished chrome trip lever.
- 1.28 gpf (4.8 lpf).
- 2-1/8" (54 mm) plastic trapway.
- Patented ReadyLock™ installation system
- 12" (305 mm) rough-in.
- Includes Glenbury[™] Quiet-Close[™] with Grip-Tight seat.
- Less supply.
- 9-5/8" (244 mm) x 7-3/8" (187 mm) water area.
- 27-3/4" (705 mm) x 18" (457 mm) x 28-1/4" (718 mm).
- Floor mount/Floor outlet.

Optional Accessories

K-5383 10" Rough-in Full Skirt Trap and Attachment System K-5381 14" Rough-in Full Skirt Trap and Attachment System K-4733 Toilet Seat

K-7637 Angle Supply with Stop (single)

Components

Additional included component/s: Tank cover, Trip Lever, K-4733 Seat, and ReadyLock™ installation system.





Codes/Standards

ASME A112.19.2/CSA B45.1 DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC)

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.


Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	NY	Dune
	95	Ice™ Grey
	G9	Sandbar
	33	Mexican Sand™
	K4	Cashmere
	58	Thunder™ Grey
	7	Black Black™





Memoirs® Classic

Comfort Height® Toilet K-6424



Technical Information

All product dimensions are nominal.

Toilet type: One-piece, Floor-mount

Waste Outlet: Floor

Bowl shape: Compact Elongated front

Flush type: AquaPiston
Trap passageway: 2-1/8" (54 mm)

Water Consumption

Full: 1.28 gpf (4.8 lpf)

Water surface size: 9-5/8" x 7-3/8" (244 mm x 187 mm)

Rim to water surface: 5-3/8" (137 mm)
Rough-in: 12" (305 mm)
Seat-mounting holes: 5-1/2" (140 mm)

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.

