



Single-handle Bathroom Sink Faucet K-73050-7

Features

- Metal construction.
- Cylindrical handle with unique actuation.
- Leak-free ceramic disc valves exceed industry standards by two times for a lifetime of use.
- Temperature memory allows faucet to be turned on and off at any temperature setting.
- High-temperature limit setting for added safety.
- Single-hole mounting.
- Durable KOHLER finishes resist corrosion and tarnishing.
- Complete range of faucets, accessories and showering components to coordinate a full bathroom.
- 1.2 gal/min (4.5 l/min) maximum flow rate [max at 60 psi (4.1 bar)]
- Not for use with Lavatories with centerset drillings





Codes/Standards

ASME A112.18.1/CSA B125.1 NSF 61 NSF 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC) ADA ICC/ANSI A117.1

KOHLER[®] Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description




CP Polished Chrome

TT Vibrant Titanium



Composed™

Single-handle Bathroom Sink Faucet K-73050-7



Technical Information

All product dimensions are nominal.	
Valve body:	Cast Brass
Drain with overflow:	YES
Drain tailpiece	YES
included:	
Spout:	

KOHLER, Faucets

Spout reach: 5-15/16" (151 mm)

Faucet:

Flow rate:	1.2 gal/min (4.5 l/min)
Pressure:	60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.

