

Composed™ Single-handle Bidet Faucet K-73176-4

Features

- Metal construction.
- Leak free ceramic disc valves exceed industry standards by two times for a lifetime of use.
- Temperature memory allows faucet to be turned on and off at any temperature setting.
- High-temperature limit setting for added safety .
- Single-hole mounting.
- Flexible connections for easy installation.
- Durable KOHLER finishes resist corrosion and tarnishing.
- Complete range of faucets, accessories and showering components to coordinate a full bathroom.
- 1.5 gal/min (5.7 l/min) maximum flow rate [max at 60 psi (4.1 bar)]



Codes/Standards ASME A112.18.1/CSA B125.1

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.


Color	Code	Description
	СР	Polished Chrome
	TT	Vibrant Titanium





Composed™

Single-handle Bidet Faucet K-73176-4



Technical Information

All product dimensions are nominal.

Valve body: Cast Brass
Drain with overflow: YES

Drain tailpiece YES

included: **Spout:**

Spout reach: 4-5/8" (118 mm)
Handle clearance: 1-9/16" (40 mm)

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

