

Composed™

Single-handle Tall Bathroom Sink Faucet K-73159-7

Features

- Metal construction.
- Pure handle with unique actuation.
- Temperature memory allows faucet to be turned on and off at any temperature setting.
- High-temperature limit setting for added safety.
- Leak free ceramic disc valve allows both volume and temperature control.
- Durable KOHLER finishes resist corrosion and tarnishing.
- Single-hole mounting.
- Complete range of faucets, accessories and showering components to coordinate a full bathroom.
- 1.2 gal/min (4.5 l/min) maximum flow rate [max at 60 psi (4.1 bar)]
- Not compatible with lavatories with centerset drillings





Codes/Standards

ASME A112.18.1/CSA B125.1 NSF 61 NSF 372 All applicable US Federal and State material

regulations
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.


| Color | Code | Description |
|-------|------|------------------|
| | CP | Polished Chrome |
| | TT | Vibrant Titanium |





Composed™

Single-handle Tall Bathroom Sink Faucet K-73159-7



Technical Information

All product dimensions are nominal. Valve body: Cast Brass

Drain with overflow: YES
Drain tailpiece YES

included: **Spout:**

Spout reach: 7-1/8" (181 mm)

Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Pressure: 60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.

