

Coralais® Centerset Bathroom Sink Faucet K-P15182-4RA

Features

- Metal construction.
- One-piece, self-contained ceramic disc valve allows both volume and temperature control.
- Temperature memory allows faucet to be turned on and off at any temperature setting.
- Flexible connections.
- 4-3/16" (107 mm) stationary spout reach.
- Metal pop-up drain.
- Red/blue indexing.
- Project pack six per case.
- 1.2 gal/min (4.5 l/min) maximum flow rate [max at 60 psi (4.14

Optional Accessories

1160594 Large Spray Aerator 0.35 gpm (1.3 l/min)





CSA B651 ADA

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1

NSF 61

NSF 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

EPA WaterSense®

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

CSA B651

OBC

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description


Polished Chrome CP





Coralais®

Centerset Bathroom Sink Faucet K-P15182-4RA



Technical Information

All product dimensions are nominal.

Valve body: Plastic
Drain included: YES
Drain with overflow: YES
Drain tailpiece YES

included:

Spout:

Spout reach: 4-3/16" (107 mm) Handle clearance: 3-3/8" (86 mm)

Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Pressure: 60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

