

COMMERCIAL-GRADE

RESIDENTIAL ELECTRIC WATER HEATERS

PROLINE® SPECIALTY ELECTRIC COMMMERCIAL-GRADE RESIDENTIAL

TABLE TOP

• Features a convenient flat porcelain surface at 36" height, providing extra "counter space" wherever installed. All plumbing and electrical connections are made through the back of the water heater. This heater is equipped with a PEX crosslinked polymer dip tube.

POINT-OF-USE

 Designed for low-demand, such as office lavatories or buildings with remote restrooms.

COMPACT

• Side-mounted plumbing and electrical connections (optional top-mounted water connections for field conversion). Designed for installation under a counter, in a crawl space or in other tight spaces.

BLUE DIAMOND® GLASS COATING

• Provides superior corrosion resistance compared to industry standard glass lining.

ENHANCED-FLOW BRASS DRAIN VALVE

- Our standard residential water heaters have a solid brass, tamper resistant, enhanced flow, ball type, drain valve.
- Uses a standard female hose fitting that allows for fast and easy draining during maintenance.
- Designed for easy operation, this valve includes an integral screwdriver slot that features a ¼ turn (open/close) radius, which not only permits full straightthrough water flow but also a quick and positive shut off.

CODE COMPLIANCE

- Meets UBC, CEC and HUD National Codes.
- Meets the thermal efficiency and standby loss requirements of the U.S. Department of Energy and current edition of ASHRAE/ IES 90.1.
- Complies with the Federal Energy Conservation Standards effective April 16, 2015, in accordance with the Energy Policy and Conservation Act (EPCA), as amended.

APPROVED FOR MANUFACTURED Housing

• All residential electric water heaters are compliant with HUD Standards for mobile homes/manufactured housing.

CERTIFIED TO UL 174 FOR Household Electric Water Heaters

CSA CERTIFIED AND ASME RATED T&P RELIEF VALVE

DESIGN-LISTED BY UNDERWRITERS LABORATORIES

- Certified at 300 PSI test pressure and 150 PSI working pressure.
- Listed according to UL 174 standards governing storage tank-type electric water heaters.

6-YEAR LIMITED TANK AND PARTS WARRANTY

• For complete information consult the written warranty or State Water Heaters.







SOLID. STATE.



COMMERCIAL-GRADE

RESIDENTIAL ELECTRIC WATER HEATERS

Model Number	Gallon	First Hour	Energy	Element Wattage		Recovery @ 90°F Rise	Dimensions in Inches			Approx. Shipping
	Capacity	Rating Gallon	Factor	Standard	Maximum	Gallons Per Hour	A	В	C	Weight (lbs)
COMPACT MODELS				120V	240V					
ESG 6 SOMS K	6	N/A	N/A	1650	3000	8	15-1/4	10-3/4	14-1/4	35
ES6 10 SOMS K	10	N/A	N/A	1650	6000	8	18-1/4	12-1/4	16	41
ES6 20 SOMS K	19	N/A	N/A	2500	6000	11	24-3/4	18-5/8	18	68
ES6 20 SOMT K	19.9	N/A	N/A	2500	6000	11	31-5/8	25-3/4	16	68
LOWBOY SIDE-CONNECT MODEL				240V						
ENG 30 DOMBS*	28	39	0.95	4500	6000	21	30	21-3/4	22	101
ENG 30 DOMS	28	39	0.95	4500	6000	21	31-1/4	21-3/4	24	115
ENG 40 DOMBS*	38	47	0.95	4500	6000	21	31-3/4	24	24	118
EN6 40 DOMS	38	44	0.95	4500	6000	21	33-1/2	24	26	118
TABLE TOP MODEL				240V						
ENG 38 20TT	38	45	0.88	4500	5500	21	36	24	25	150
POINT-OF-USE MODELS	INT-OF-USE MODELS			120V						
ESG 2 SSUS K	2.5	N/A	N/A	1500 @ 120V		7	13-3/4	11	13-3/4	20

*Models ship with a supplied insulation blanket.


Dimensions and specifications subject to change without notice in accordance with our policy of continuous product improvement.


[†]Top mounted T&P adds approximately 3" additional to overall height. Water connection is 3/4" on Table Top and Compact models and 1/2" NPT on Point-Of-Use models.

ES6 20 SOMT

Compact Models

õ





ES6 6 SOMS

ES6 10 SOMS ES6 20 SOMS






Table Top Model




EN6 38 20TT

Lowboy



ENG 30 DOMS, ENG 30 DOMBS, ENG 40 DOMS, ENG 40 DOMBS

Point-Of-Use



ES6 2 SSUSK

FOR MORE INFORMATION CONTACT: STATE WATER HEATERS 500 TENNESSEE WALTZ PARKWAY, ASHLAND CITY, TN 37015 • 800-365-0024 TOLL-FREE USA • STATEWATERHEATERS.COM