



SELECT®

ENHANCED HEATING ELEMENTS

- Dual 4500 watt elements for faster recovery and reliable operation.*
- Incoly stainless steel lower element lasts longer than a standard copper element.

SELF CLEANING DIP TUBE

- Helps reduce lime and sediment buildup, maximizes hot water output. Made from long-lasting PEX cross-linked polymer.

HIGH ENERGY FACTORS

- Eco-friendly non-CFC foam insulation, heat traps and other features combine to yield a higher Energy Factor that maximizes savings on operating costs.

COREGARD™ ANODE ROD

- Our anode rods have a stainless steel core that extends the life of the anode rod allowing superior tank protection far longer than standard anode rods.

BLUE DIAMOND® GLASS COATING

- Provides superior corrosion resistance compared to industry-standard glass lining.

ENHANCED-FLOW BRASS DRAIN VALVE

- Our residential water heaters have a solid brass, tamper resistant, enhanced-flow, ball type, drain valve.
- Uses a standard female hose fitting that allows for fast and easy draining during maintenance.
- Designed for easy operation, this valve includes an integral screwdriver slot that features a ¼ turn (open/close) radius, which not only permits full straight-through water flow but also a quick and positive shut off.

*Model EN6 20 SOLS has a single element.

CODE COMPLIANCE

- Meets UBC and ICC National Codes and listed with CEC.
- Complies with the Federal Energy Conservation Standards effective April 16, 2015, in accordance with the Energy Policy and Conservation Act (EPCA), as amended.

APPROVED FOR MANUFACTURED HOUSING

- All residential electric water heaters are compliant with HUD Standards for mobile homes/manufactured housing.

CERTIFIED TO UL 174 FOR HOUSEHOLD ELECTRIC WATER HEATERS

CSA CERTIFIED AND ASME RATED T&P RELIEF VALVE

DESIGN-LISTED BY UNDERWRITERS LABORATORIES

- Certified at 300 psi test pressure and 150 psi working pressure.
- Listed according to UL 174 standards governing storage tank-type electric water heaters.

6-YEAR LIMITED TANK AND PARTS WARRANTY

- For complete information, consult written warranty or go to statewaterheaters.com.



SOLID. STATE.



Residential Electric

Water Heaters

| Model Number | Gallon Capacity | First Hour Rating Gallon | Energy Factor | Recovery @ 90°F Rise Gallon Per Hour | Element Wattage 240V | | Dimensions in Inches | | | Approx. Shipping Weight (lbs) |
|----------------------------------|-----------------|--------------------------|---------------|--------------------------------------|----------------------|---------|----------------------|--------|--------|-------------------------------|
| | | | | | Standard | Maximum | A | B | C | |
| Tall Models | | | | | | | | | | |
| †ENG 30 DORT | 30 | 47 | 0.95 | 21 | 4500 | 6000 | 46-1/2 | 39-1/2 | 19 | 95 |
| †ENG 40 DORT | 40 | 51 | 0.95 | 21 | 4500 | 6000 | 60-1/4 | 53-1/4 | 20 | 118 |
| †ENG 50 DORT | 50 | 73 | 0.95 | 21 | 4500 | 6000 | 60-1/2 | 51-1/4 | 20-1/2 | 125 |
| †ENG 55 DORT | 55 | 76 | 0.94 | 21 | 4500 | 6000 | 56-1/2 | 48-1/2 | 24 | 145 |
| Short Models | | | | | | | | | | |
| ENG 30 DOBS* | 30 | 48 | 0.95 | 21 | 4500 | 6000 | 39 | 30-1/2 | 20 | 95 |
| †ENG 30 DORS | 30 | 49 | 0.95 | 21 | 4500 | 6000 | 39-3/4 | 30-1/2 | 22 | 94 |
| †ENG 40 DORS | 40 | 55 | 0.95 | 21 | 4500 | 6000 | 49-3/4 | 40-3/4 | 20-1/2 | 109 |
| †ENG 50 DORS | 50 | 62 | 0.95 | 21 | 4500 | 6000 | 49-1/4 | 40-3/8 | 23 | 161 |
| Lowboy Top Connect Models | | | | | | | | | | |
| ENG 20 SOLS | 19.5 | N/A | N/A | 21 | 4500 | 6000 | 30 | 21-1/4 | 20 | 65 |
| ENG 30 DOLBS* | 28 | 40 | 0.95 | 21 | 4500 | 6000 | 30 | 21-3/4 | 20 | 90 |
| †ENG 30 DOLS | 28 | 43 | 0.95 | 21 | 4500 | 6000 | 31-1/4 | 21-3/4 | 24 | 115 |
| ENG 40 DOLBS* | 38 | 44 | 0.95 | 21 | 4500 | 6000 | 32 | 24 | 23 | 118 |
| †ENG 36 DOLS | 36 | 46 | 0.95 | 21 | 4500 | 6000 | 32 | 24 | 24 | 118 |
| †ENG 50 DOLBS* | 48 | 57 | 0.95 | 21 | 4500 | 6000 | 34 | 25 | 26-1/2 | 172 |

Male 3/4" water connections on 8" center.

*Models ship with supplied insulation blanket.

†For 10-year tank and 6-year parts limited warranty, change "N6" to "SX" in select models and "R" to "N" in tall and short model number (example: ESX 40 DONT).



ENG 20 SOLS is a single element configuration only

Optional top T&P location #2 is used on ENG 50 DORT, ENG 55 DORT, ENG 40 DORS and ENG 50 DORS.

Optional top T&P location #3 is used on ENG 50 DOLBS, ENG 30 DOLBS, ENG 40 DOLBS and ENG 36 DOLS.

Top T&P is not available on the 10 year model ESX 50 DOLBS.

Dimensions and specifications subject to change without notice in accordance with our policy of continuous product improvement.



FOR MORE INFORMATION ON SELECT® CONTACT: STATE WATER HEATERS 500 TENNESSEE WALTZ PARKWAY, ASHLAND CITY, TN 37015 • 800-365-0024 TOLL-FREE USA • STATEWATERHEATERS.COM