




Project: Date:

Prepared by:

Comments:



FEATURES

- 5 Year Warranty
- Energy Savings of up to 30%
- Only 25.20 Watts Usage
- Lumen Maintenance over 70% @ 50,000+ Hours
- Brush Nickel Finish
- Instant On at Full Brightness
- No UV/IR Radiation, No Toxic Mercury
- Noise Free
- 10% - 100% Dimmable with 120V Triac Dimmer

OPTICS

- Frosted Glass Shades
- CRI 82

APPLICATIONS

- Surface Mount Ceiling Application for General Lighting in Homes
- Retail Store Accent Lighting
- Museums, Galleries, Showrooms
- Hotels, Hospitality Areas

CERTIFICATIONS

- cETLus Listed
- Lighting Facts Listed
- Energy Star Listed

SPECIFICATIONS

Part Number: EVT102027-35

Warranty: 5 Years
Kelvin Temperature (CCT): 2700K
Wattage: 25.20W
Lumens: 1,890 lm
Efficacy: 75 lm/W
CRI: 82
Input Voltage: AC 120

Certifications: cETLus Listed
DLC Listed: Yes
Expected Life: 50,000 hrs
Max. Ambient Temperature: 45° C
Min. Ambient Temperature: -20° C
Dimmable: 120V Triac Dimmer
Watt Equivalence: 140 Watt Incandescent

TECHNICAL

Weight: 4.6 lbs
Length: 31.10"
Product Height: 6.30"
Product Width: 6.10"

R-Value: 50
Power Factor: 0.98
LED Beam Angle: 60°
THD: <20%






Project: Date:

Prepared by:

Comments:

DIMENSIONS



LIGHTING FACTS

Envirotech

LED lighting facts
A Program of the U.S. DOE

Light Output (Lumens) 1890
Watts 25.2
Lumens per Watt (Efficacy) 75

Color Accuracy
 Color Rendering Index (CRI) 82

Light Color
 Correlated Color Temperature (CCT) 2700 (Warm White)

2700K 3000K 4500K 6500K

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: ZMBK-EGN8YW (12/4/2015)
 Model Number: EVT102027-Y
 Type: Luminaire - Decorative