LED15011A-35 LED WALL SCONCE





FEATURES

- Energy Savings of up to 83%
- Lumen Maintenance over 70% @ 50,000+ Hours
- No UV/IR Radiation, No Toxic Mercury
- Steel Trim in Brushed Nickel Finish
- Die Formed of 22 Gauge Plated Steel
- Replaces 60W Incandescent
- ADA Approved

<u>OPTICS</u>

Acrylic White Lens

APPLICATIONS

- Hallways
- Corridors
- Bathrooms
- Lobbies

CERTIFICATIONS

- UL/cUL Listed
- Energy Star
- Lighting Facts

SPECIFICATIONS

Part Number: LED15011A-35

Manufacturer Limited Warranty:3 YearsCertifications:UL ListedKelvin Temperature (CCT):3000KDLC Listed:No

Wattage: 10.2W
Average Hour Life: 50,000 hrs
Lumens: 889 lm
Max. Ambient Temperature: 45°C

Efficacy: 92.8 lm/w Min. Ambient Temperature: 45°C

Min. Ambient Temperature: -20°C

 CRI:
 80
 Power Factor:
 >0.9

 Dimmable:
 0-10V Dimming
 THD:
 <20%</td>

Input Voltage: DC 120V

TECHNICAL

 Weight:
 2.77lbs
 Product Width:
 7"

 Length:
 3.5
 LED Beam Angel:
 120

Product Height: 9.75" LED Type: Integrated LED Array







LED15011A-35 LED WALL SCONCE



LINE DRAWINGS

178 [7]

LIGHTING FACTS

