MODA[™] WASHING MACHINE OUTLET BOX

Job Name:	_ Item #:
Location:	
Engineer:	_ Contractor:
PO#:	_ Tag:
Representative:	-
•	

SPECIFICATION

Oatey MODATM washing machine outlet boxes shall be used in residential or commercial applications requiring supply valves and a waste drain recessed in the wall. The MODATM washing machine assembly contains a valve box and a drain box, connected by inter-locking wing flanges that can be easily disassembled and re-assembled. Box shall be manufactured of PVC, allowing solvent welded joints to be prepared in accordance with ASTM D2855 for PVC drainage systems (without the use of specialty cements). The inter-locking wing flanges shall allow installation on a single stud, between two studs or on separate walls, without the need for additional components. Valves shall be a two-piece design, permitting field replacement, and shall be secured with a stainless steel retention clip. Valves are available with or without water hammer arrestors and shall be installed upright or inverted. The assembly shall include a removable quarter-turn knock out plug for DWV testing, and shall include an emergency drain port for added protection from hose leaks.

Accessory Components Included.

Side Brackets (2)

F

MATERIALS

Outlet Box & Brackets	PVC
Valve Body	Forged Brass C37700
Valve Retention Clip	Stainless Steel
Valve O-Rings	NSF Approved EPDM (2)

PERFORMANCE SPECIFICATIONS

Temperature Rating (Valve)	250° F / 121° C
Max Testing Pressure (Valve)	100 psi (Air) / 250 psi (Water)

LISTINGS & CODE APPROVALS

Valves	ASME A112.18.1 / CSA B125.1	VPO
Water Hammer Arrestors	ASSE 1010	\sim
Boxes	IAPMO-Listed, , PS-54	
DIMENSIONS		

[A]:	Assembled Width	14.13''	[E]:	Bracket Length	8.00″
[B] :	Box Depth	3.38"	[F]:	Faceplate Width	6.00''
[C]:	Box Height	4.85''	[G]:	Faceplate Height	6.45′′
[D]:	Bracket Width	4.00″	[H]:	Faceplate Depth	1.25″

PRODUCT SELECTOR

No Hammer Arrestors					Hammer Arrestors						
	37601	WMOB, Copper, NoHam, Std Pk		37617	WMOB, Copper, NoHam, Cont Pk		37609	WMOB, Copper, Ham, Std Pk		37625	WMOB, Copper, Ham, Cont Pk
	37603	WMOB, F1807-Brass, NoHam, Std Pk		37619	WMOB, F1807-Brass, NoHam, Cont Pk		37611	WMOB, F1807-Brass , Ham, Std Pk		37627	WMOB, F1807-Brass, Ham, Cont Pk
	37604	WMOB, F2159-PPSU, NoHam, Std Pk		37620	WMOB, F2159-PPSU, NoHam, Cont Pk		37612	WMOB, F2159-PPSU, Ham, Std Pk		37628	WMOB, F2159-PPSU, Ham, Cont Pk
	37605	WMOB, F1960-Brass, NoHam, Std Pk		37621	WMOB, F1960-Brass, NoHam, Cont Pk		37613	WMOB, F1960-Brass, Ham, Std Pk		37629	WMOB, F1960-Brass, Ham, Cont Pk
	37606	WMOB, F1960-PPSU, NoHam, Std Pk		37622	WMOB, F1960-PPSU, NoHam, Cont Pk		37614	WMOB, F1960-PPSU, Ham, Std Pk		37630	WMOB, F1960-PPSU, Ham, Cont Pk
	37602	WMOB, CPVC, NoHam, Std Pk		37618	WMOB, CPVC, NoHam, Cont Pk		37610	WMOB, CPVC, Ham, Std Pk		37626	WMOB, CPVC, Ham, Cont Pk
	37608	WMOB, Push Cnc, NoHam, Std Pk					37616	WMOB, Push Cnc, Ham, Std Pk			

Standard packs shipped with faceplates on boxes, contractor packs ship with faceplates packaged separately.

All products sold in case packs of 12.

Access BIM/Revit content through www.oatey.com



Test Plua

Faceplates (2)

Center Support (For Added Rigidity)

Sticker Cover (2)





