PFX146

Stainless Steel Dishwasher

Reinforced Flexible Connectors



Product Features

• Working Temperature: 40°F to 140°F

• Working Pressure: up to 125 PSI maximum

• Internal Hose: reinforced PVC

• Outer Wire Braid: 304 stainless steel

Barb: low lead brass alloyElbow Adaptor: brass alloy

• Metal Nuts: nickel-plated brass alloy

• Ferrule: nickel-plated brass alloy

• Washer: Santoprene rubber



PFX146352

Installation Instructions

- For use with water in accessible locations only
- Metal Nuts: hand tighten plus 1/4 turn with wrench
- Do not over tighten nuts
- Check for leaks before leaving job site
- · Inspect regularly for general fitness and replace if damaged, corroded or worn
- Do not expose to corrosive chemicals

Models and Product Certifications

Model #	Description	UPC	Low Lead Compliant
PFX146350	3/8" COMP X 3/8" COMP X 48" SS Dishwasher (with elbow)	✓	✓
PFX146352	3/8" COMP X 3/8" COMP X 60" SS Dishwasher (with elbow)	✓	✓
PFX146354	3/8" COMP X 3/8" COMP X 72" SS Dishwasher (with elbow)	✓	✓
PFX146365	1/2" COMP X 1/2" COMP X 84" SS Dishwasher (with elbow)	✓	✓

Warranty and Listing Certification

This PROFLO product carries a 1-year limited warranty. IAPMO listed to ASME A112.18.6-2009 and CSA B125.6-2009 IAPMO listed to NSF/ANSI 61 and NSF/ANSI 372