

PF146

Stainless Steel Washing Machine

Reinforced Flexible Connectors



Product Features

- Working Temperature: 40°F to 140°F
- Working Pressure: up to 125 PSI maximum
- Internal Hose: reinforced PVC
- Outer Wire Braid: 304 stainless steel
- Barb: low lead brass alloy
- Metal Nuts: nickel-plated brass alloy
- Ferrule: nickel-plated brass alloy
- Washer: Santoprene rubber



PF146816

Installation Instructions

- For use with water in accessible locations only
- Metal Nuts: hand tighten only
- Do not over tighten nuts
- Check for leaks before leaving job site
- Inspect regularly for general fitness and replace if damaged, corroded or worn
- Do not expose to corrosive chemicals

Models and Product Certifications

Model #	Description	UPC	Low Lead Compliant
PF146814	3/4" FHT X 3/4" FHT X 48" SS Washing Machine Hose	✓	✓
PF146815	3/4" FHT X 3/4" FHT X 60" SS Washing Machine Hose	✓	✓
PF146816	3/4" FHT X 3/4" FHT X 72" SS Washing Machine Hose	✓	✓

Warranty and Listing Certification

This PROFLO product carries a 1-year limited warranty.

IAPMO listed to ASME A112.18.6-2009 and CSA B125.6-2009

IAPMO listed to NSF/ANSI 61 and NSF/ANSI 372