


Glass Fillers

Architect/Engineering Specifications:

Wall mount glass filler with polished chrome plated brass body, adjustable flow outlet, push back arm, 3/8" NPT female inlet and ϕ 2" adjustable slip flange. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372. Meets ADA ANSI/ICC A117.1 requirements.



Features & Benefits:

- Wall mount glass filler
- Adjustable flow outlet
- Instantaneous shut-off
- 3/8" NPT female inlet
- Ø2" adjustable slip flange
- Material: Polished chrome plated brass body
 chrome plated metal flange and thermoplastic arm

Product Compliance:

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)
- ANSI A117.1 (ADA)

Warranty: One Year (Limited)

Performance Data:

- Pressure: 20 125 psi
- Temperature: 40 °F 140 °F
- Flow Rate: 0.25 GPM min @ 60 psi 2.50 GPM max @ 60 psi











