
Double Pantry Faucet

Architect/Engineering Specifications:


8" deck mount mixing faucet with polished chrome plated brass body, swivel outlet (less nozzle), compression cartridges with spring checks, lever handles and 1/2" NPT female inlets. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372. Meets ADA ANSI/ICC A117.1 requirements.

Job Name	
Model Specified	Quantity
Variations Specified	
Date	




Features & Benefits:

- 8" deck mount mixing faucet with polished chrome plated brass body
- Swivel outlet accepts T&S swing nozzles and EasyInstall risers
- Quarter-turn Eterna compression cartridges with spring checks to prevent cross flow of water
- Lever handle w/ color coded indexes
- 1/2" NPT female eccentric inlets w/ Ø 2" flanges
- Adjustable centers from 7 3/4" to 8 1/4"
- Material: Polished chrome plated brass body and chrome plated metal handles



Product Compliance:



NSF 61 - Section 9

NSF 372 (Low Lead Content)

ANSI A117.1 (ADA)

Warranty: One Year (Limited)





Performance Data:

Pressure: 20 - 125 psi Temperature: 40°F - 140°F Flow Rate: 30.01 GPM @ 60 psi

(Outlet Device &/or Final Configuration May Reduce Flow Rate)

Optional Handles Optional Cartridges

- ☐ 4" Wrist Action
- □ Lever (Standard)

□ 4-Arm

- □ Quarter-Turn Cerama w/ Check Valve
 - □ Quarter-Turn Eterna w/ Spring Check (Standard)









