

# **Architect/Engineering Specifications:**

Deck mount bubbler with polished chrome plated brass body, flexible rubber mouth guard, adjustable outlet flow control, metering cartridge, push button cap and 1/2" NPSM male inlet with coupling nut. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372. Meets ADA ANSI/ICC A117.1 requirements

Job Name	
Model Specified	Quantity
Variations Specified	
Date	







### Features & Benefits:

- Deck mount bubbler with polished chrome plated brass body
- Flexible rubber mouth guard
- Hidden flow control screw provides adjustable outlet flow
- Metering cartridge
- Adjustable metering cycle, 10-30 seconds
- Cold push button cap
- 1/2" NPSM male inlet with coupling nut
- Mounting flange can provide anti-rotation with available anti-rotation screw kit (sold separately)
- Material: Polished chrome plated brass body, flexible rubber mouth guard

#### **Optional Cartridges**

- □ Push Button Metering (Standard)
- ☐ Wrist Action Metering
- ☐ Pivot Action Metering
- ☐ Fast Self-Closing

## **Product Compliance:**

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)
- ANSI A117.1 (ADA)

Warranty: One Year (Limited)

### Performance Data:

Pressure: 20 - 125 psi
Temperature: 40°F - 140°F

Flow Rate:

@ 4" Distance = 0.32 GPM @ 60 psi @ 8" Distance = 0.43 GPM @ 60 psi













