

Architect/Engineering Specifications:

Deck mount bubbler with polished chrome plated brass body and flexible mouth guard, adjustable outlet flow control, fast self-closing cartridge, lever handle and 1/2" NPSM male inlet with coupling nut. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372. Meets ADA ANSI/ICC A117.1 requirements.

Job Name	
Model Specified	Quantity
Variations Specified	
Date	







Features & Benefits:

- Deck mount bubbler with polished chrome plated brass body and flexible mouth guard
- Hidden flow control screw provides adjustable outlet flow
- Fast self-closing cartridge
- Lever handle w/ vandal resistant screw
- 1/2" NPSM male inlet with coupling nuts
- Mounting flange can provide anti-rotation feature w/ optional set screws
- Material: Polished chrome plated brass body, flexible rubber mouth guard and chrome plated metal handle

Product Compliance:

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)
- ANSI A117.1 (ADA)



ADA Compliant

Warranty: One Year (Limited)

Performance Data:

Pressure: 20 - 125 psi

Temperature: 40°F - 140°F

Flow Rate:

@ 4" Distance = 0.32 GPM @ 60 psi

@ 8" Distance = 0.43 GPM @ 60 psi

Optional Cartridges

- □ Push Button Metering
- □ Wrist Action Metering
- ☐ Pivot Action Metering
- ☐ Fast Self-Closing (Standard)









