





## Remote Control Straight Valve Unit

### Architect/Engineering Specifications:

Remote control straight valve with brass body, 19 1/16" centerline to flange, 4-arm handle, snap-in color coded indexes, guide flange, universal joint and 3/8" NPT male inlet and outlet. Certified to ANSI Z21.15a / CSA 9.1a.

Job Name \_\_\_\_\_  
Model Specified \_\_\_\_\_ Quantity \_\_\_\_\_  
Variations Specified \_\_\_\_\_  
Date \_\_\_\_\_



### Features & Benefits:

- Remote control straight valve with brass body
- 19 1/16" centerline to bushing
- Stainless steel floating cone and removable seat
- 4-arm handle w/ snap-in color coded indexes (gas, air and vacuum included)
- $\phi$  2" guide flange w/ mounting hardware
- Universal joint
- 3/8" NPT male inlet and outlet
- Material: brass body and polished chrome plated brass handle

### Product Compliance:

- ANSI Z21.15a / CSA 9.1a (Gas Valves)

**Warranty:** One Year (Limited)

### Performance Data:

- Pressure: 25 - 125 psi
  - Gas - 0.5 psi max
  - Air - 125 psi max
  - Vacuum - 30 inches of Mercury max
- Temperature: 32 °F - 125 °F

