

TAG:	

# Angle Loose Key Stop

## **Architect/Engineering Specifications:**

Flexible supply assembly with polished chrome plated brass body and loose key angle stop, 3/8" O.D. x 12" flexible copper tube, 1/2" NPT female inlet and  $\emptyset$  2 1/2" wall flange. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372.







### Features & Benefits:

- Flexible supply assembly with polished chrome plated brass body
- 3/8" O.D. x 12" flexible copper supply tube
- Loose key angle stop w/ handle and screw
- 1/2" NPT female inlet
- Ø 2 1/2" wall flange
- Material: Polished chrome plated brass body, chrome plated metal wall flange & copper supply tube

# **Product Compliance:**

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)

Warranty: One Year (Limited)

#### **Performance Data:**

Pressure: 20 - 125 psi
Temperature: 40 °F - 140 °F
Flow Rate: TBD GPM @ 60 psi









