

ULTRA LED™ 3-Way A21 Lamps

Omnidirectional



Key Features & Benefits

- Long life: up to 25,000 hours (L₇₀)
- UV and IR free
- Mercury and lead free
- RoHS compliant
- Available in 2700K & 5000K color temperatures
- Reduces energy consumption up to 85%
- Lasts up to 25 times longer than incandescent lamps
- No warm-up time, instant-on with full light output and stable color



Rated up to 25,000 hours at 70% lumen maintenance, ULTRA LED 3-Way A21 LED lamps offer years of service and reduce energy and maintenance costs. ULTRA LED 3-Way A21 LED lamps are environmentally preferred products and allow you to control energy use and light output. They are RoHS compliant and contain no mercury, lead or other hazardous materials. They emit no UV or IR radiation. A CRI of 80 ensures good color definition. The ULTRA LED 3-Way A21 lamp is available in warm 2700K and cool 5000K color temperatures.

Product Offering

Ordering Abbreviation	Color Temperature	Typical Lumens
4.5W/8.5W/15W A21 LED	2700K & 5000K	450/800/1600

Application Information

Applications

- Table lamps

Market Segments

- Residential

Application Notes

1. Operating temperature range between -20°C and +45°C (-4°F and +113°F)
2. Not for use with emergency light fixtures or exit lights
3. Use in open fixture - do not use in enclosed fixture
4. Suitable for indoor/outdoor use

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:
(1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, please see www.sylvania.com/fcc15b.



Specification Data

Catalog #	Type
Project	
Comments	
Prepared by	

Ordering Information

Item Number	Ordering Abbreviation	Wattage (W)	Base Type	Replaces	Input Voltage (V)	Average Rated Life (hrs.) ¹	CCT ²	Typical Lumens (lm) ³	CRI ⁴	Bulb Finish	ENERGY STAR®
74021	LED15A21/3WAY/0/827/RP	4.5/8.5/15	Medium	40W/60W/100W	120	25,000	2700K	450/800/1600	80	Frosted	Yes
74086	LED15A21/3WAY/0/850/RP	4.5/8.5/15	Medium	40W/60W/100W	120	25,000	5000K	450/800/1600	80	Frosted	Yes


1. Hours lifetime with 70% (L70) lumen maintenance 2. Thermally stable typical CCT (±10%) 3. Thermally stable typical lumens (±10%) 4. CRI – Color Rendering Index

Ordering Guide

LED	15	A21	/	3WAY	/	0	/	8	27	/	RP
LED Lamps	Wattage: 15	Lamp Type: A21		3 Way		0=Omnidirectional		CRI 8=80+	CCT 27=2700K		Retail Pack

Lamp Dimensions

	(A) MOL inches (mm)	(B) Diameter inches (mm)
LED15A21	5.22	2.72



Energy Savings

Basic Product Description	LED Life (hrs.)	LED Lumens	Similar Incandescent	Incandescent Life (hrs.)	Watts Saved	LED Life vs. Incandescent
LED15A21	25,000	450/800/1600	40W/60W/100W	1000	35.5/51.5/85	25X

*Energy savings over life of lamp calculated at \$0.11/kWh

LEDVANCE LLC
200 Ballardvale Street
Wilmington, MA 01887 USA
Phone 1-800-LIGHTBULB (1-800-544-4828)
www.sylvania.com

SYLVANIA and LEDVANCE are registered trademarks.
All other trademarks are those of their respective owners.
Product Licensee of Trademark SYLVANIA in General Lighting.
Specifications subject to change without notice.

[/sylvania](https://twitter.com/sylvania) [/sylvania](https://facebook.com/sylvania)

