



Product Number: 16555

Order Abbreviation: 50PAR30LN/HAL/IR/NFL25/DL 120V

General Description: Tungsten Halogen PAR30LN IR Reflector Lamp 50Watt 120Volt Medium Base NarrowFlood25 Beam Double Life

Product Information	
Abbrev. With Packaging Info.	50PAR30LNHALIRNFL25DL 120V 10/CS 1/SKU
Approx. Lumens	850
Average Rated Life (hr)	3000
Base	E26 Medium
Beam Angle (deg)	25
Beam Type	NFL
Bulb	PAR30LN
Centerbeam Candlepower (cp)	2600
Class	C (GAS)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2825
Diameter (in)	3.752
Diameter (mm)	95.30
Family Brand Name	Halogen Par30 Long Neck
Filament	CC-8
Horizontal Beam Angle (deg)	25
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	4.625
Maximum Overall Length - MOL (mm)	119.0625
Nominal Voltage (V)	120.00
Nominal Wattage (W)	50.00



Footnotes
<ul style="list-style-type: none"> • State of the Art SPL Optics • For indoor or outdoor use where not directly exposed to weather. Exposure to weather may damage the bulb. • In base up operation, heat may eventually deteriorate paper-lined or plastic sockets.