


NEXTGEN[™] SELECTRONIC® INTEGRATED PROXIMITY LAVATORY FAUCET

SMARTHERM™ SAFETY SHUT-OFF & ABOVE DECK MIXING, BASE MODEL



PWRX® BATTERY SYSTEM

- Battery Life: 13 years @ 4,000 uses per month.
- Reduces the downtime and maintenance costs associated with changing batteries.

AC TRANSFORMERS

- UL 1310, Class 2 certified.
- Universal Input Voltage: 100 240 VAC, 50/60 Hz.
- Can run up to 15 faucets and/or flush valves at a time.

FEATURES:

- SmarTherm[™] Safety Shut-Off: Integral thermostatic hot water temperature limiter meets ASSE 1070 without a separate thermostatic mixing valve.
- Above-Deck Mixing: Allows user to manually adjust temperature. Adjustable hot limit stop. Red & blue indicators.
- Dual Inlets: For hot and cold water. Check valves included to prevent cross flow. Filter screens protect the solenoid valve from debris.
- · Hygienic, touch-free operation
- Clean, Integrated Design: All electronics contained in faucet spout. No control box below deck.
- Easy Installation & Maintenance: Faucet installs from the top. All serviceable parts are easily accessible.
- Flexible Selectronic® Platform with programmable sensor and interchangeable power supplies.
- Self-Cleaning Solenoid Reduces Maintenance: Integral wiper spring prevents clogging and run-on. Silicon seals.
- Adjustable Range: Detection zone can be adjusted manually or with optional remote control.
- Fail-Safe: Faucet automatically shuts off upon loss of power or dead battery. No reset required.
- Optional Remote Control Allows for Customization
 - **Auto Purge:** Periodically purges stagnant water from faucet and supply lines. Timing is adjustable.
 - **Safety Timer:** Turns water off if the sensor is blocked for 55 seconds. Frequency and duration are adjustable.
 - Cleaning and Thermal Disinfection
- **Lead-Free:** Faucet contains ≤ 0.25% total lead content by weighted average.weighted average.

MODEL NUMBER:

■ BASE UNIT (Does not include power supply)

- 775B.303 0.35 gpm pressure compensating, vandal-resistant multi-laminar spray.
- □ 775B.305 0.5 gpm pressure compensating, vandal-resistant multi-laminar spray.
- ☐ 775B.315 1.5 gpm pressure compensating, vandal-resistant laminar flow outlet with adjustable face.

■ POWER KITS (Must be purchased separately)

- □ PK00.PAC Includes universal Plug-In AC transformer and Single AC Adapter.
- □ PK00.MAC Includes Multi-AC Adapter and 10' extension cable.
- □ PK00.HAC Includes universal Hard-Wired AC transformer, Single AC Adapter and 10' extension cable.
- PK00.WRK Includes PWRX battery pack and holder.

■ OPTIONAL Battery Back-up

□ PK00.BBU Allows faucet to continuously operate during a power failure.

■ OPTIONAL 4" and 8" Deck Plates

- □ 775P.400 4" metal deck plate with 1/4" fixation studs and quick spin nuts. Includes fixation screw that prevents the spout from rotating.
- □ 775P.800 8" metal deck plate with 1/4" fixation studs and quick spin nuts. Includes fixation screw that prevents the spout from rotating.

■ OPTIONAL Remote Control

605XRCT Remote control adjusts setup parameters and allows for customization of functions. Can be used to program all Selectronic faucets and flush valves.

DESCRIPTION:

Deck-mount electronic faucet with proximity operation. Integrated design with sensor, solenoid valve and electronics enclosed in the spout. Integral thermostatic hot water temperature limiter is ASSE 1070 certified. Above-deck mixing with hot limit safety stop and red / blue indicators. Water pressure range from 20 - 120 psi. Vandal-resistant single-post mounting. Dual inlets for hot and cold water. Pre-installed 24" flexible stainless steel inlet hoses with integral strainer and 3/8" compression fitting.

RECOMMENDED SPECIFICATION:

Electronic, sensor-operated lavatory faucet shall feature a programmable sensor and an electronically operated self-cleaning solenoid valve with chemical resistant silicon seals. Integrated design with all electronics enclosed in the spout. Faucet meets ASSE 1070 without a separate thermostatic mixing valve. Features an above deck mixing handle with hot limit safety stop and red / blue indicators. Shall also feature a vandal resistant metal body with single-post mounting. Shall meet ANSI A112.18.1, ANSI 117.1 and ASSE 1070 codes. Model shall be American Standard # 775B.30__.002

© 2017 AS America Inc. 6/17



NEXTGEN™ SELECTRONIC® INTEGRATED PROXIMITY LAVATORY FAUCET

SMARTHERM™ SAFETY SHUT-OFF & ABOVE DECK MIXING, BASE MODEL

CODES AND STANDARDS


These products meet or exceed the following codes and standards:


ANSI A117.1 ASME A112.18.1 CSA B 125 NSF 372 ASSE 1070-2015 NSF 61




MEETS THE AMERICAN DISABILITIES ACT GUIDELINES AND ADA ANSI A117.1 REQUIREMENTS FOR ACCESSIBLE AND USABLE BUILDING FACILITIES-CHECK LOCAL CODES

FINISHES:	
Polished Chrome	.002
Brushed Nickel	.295







PART OF LIXIL