3 Step HVAC Nitrogen Purging Regulator

- The EASIEST way to install line sets -



Global Gas Management Technology

Enterprises | Innovator | Medica | Westwinds



VN-650

VN-500

VN-250

650 PSI test pressure


500 PSI test pressure

250 PSI test pressure

- Preset Purge (25-35 CFH), Braze (3-6 CFH) and Pressure Test (650 PSI, 500 PSI or 250 PSI) Settings
- Regulator and Flowmeter in ONE
- Hand-tight Cylinder Connection



Why Use Nitrogen when Brazing HVAC Line Sets?



Copper tubing brazed with nitrogen purge.



Copper tubing brazed without nitrogen purge. *Notice the black oxide deposits.



Large, easy to read selector knob Industry standard ½" SAE TST, PRG, BRZ, OFF flair outlet TST PRG CGA-580 Rugged connection solid brass body

Part #	Description
VN-650	Nitrogen Purging/Test Regulator w/650 PSI Test Pressure
VN-500	Nitrogen Purging/Test Regulator w/500 PSI Test Pressure
VN-250	Nitrogen Purging/Test Regulator w/250 PSI Test Pressure

1 year warranty, Made in the USA



Global Gas Management Technology

Enterprises | Innovator | Medica | Westwinds

cylinder