


Luxura® 6032 Skirted Bath Technical Specifications

Letter	Description	Soaker	Whirlpool	Pure Air	Each component requires a separate, dedicated GFCI protected circuit
-	Drain Location		LH/RH Drain		
-	Pump/Blower Location		LH/RH Pump		GFCI Outlet (60Hz)
-	Cutout Template		N/A		
-	Drop-in Cutout Dimensions (L x W)		N/A		Soaker Only
-	Total Weight	675 lbs (306 kg)	700 lbs (317 kg)	707 lbs (320 kg)	
-	Floor Loading	51lb/ft ² (247 kg/m ²)	53lb/ft ² (258 kg/m ²)		
-	Operating Gallons (Max)	50 gal (189 L)			Whirlpool Model
-	Product Weight - Empty	75 lbs (34 kg)	100 lbs (45 kg)	117 lbs (53 kg)	
-	Soaking Depth	16" (406 mm)			120V/15A 120V/15A
L	Outer Length	60" (1524 mm)			
W	Outer Width	32" (812 mm)			
H	Overall Height	20.25" (514 mm)			
A	Overflow Height	15.25" (387 mm)			
B	Long Edge to Drain Center	8.25" (210 mm)			
C	Short Edge to Drain Center	16" (406 mm)			
D	Drain Shoe Length	5.25" (133 mm)			
E	Tile Flange Height	1" (25 mm)			
F	Deck Width	3.6" (91 mm)			
G	Service Access Dimensions	12" x 18" (305 mm x 457 mm)			
I	Floor Cutout for Drain	12" x 6" (305 mm x 152 mm)			
J	Interior Dimensions (JW x JL) Bottom of Bath	45" x 19.5" (1143 mm x 495 mm)			
K	Interior Dimensions (KW x KL) Top of Bath	53.5" x 22.5" (1359 mm x 571 mm)			
L2	Interior Depth - Drain End (D)	19" (483 mm)			
M	Backrest Angle	26°			

Key Dimensions



Product shows Luxura 6032 Skirted Bath Left-Hand Model.
*Measurements inside unit represent cutout in floor to allow for drain/overflow.

NOTE

The overall dimensions are nominal with a tolerance of +0 and -0.25" (6mm).

*Deck width reflects only area indicated on detail.