




# Signa® 6042 Whirlpool And Soaking Bathtubs

Letter	Description	Whirlpool	Soaking
-	Drain Location	Center	
-	Whirlpool Pump Location	Left Hand / Right Hand	N/A
-	Cutout	58.00" x 40.00" (1473 mm x 1016 mm)	
-	Total Weight	983 lb (446 kg)	964 lb (437 kg)
-	Floor Loading	56 lb/ft² (273 kg/m²)	55 lb/ft² 269 kg/m²)
-	Operating Gallons (Max)	75 Gal (284 L)	
-	Product Weight	108 lb (49 kg)	89 lb (40 kg)
L	Outer Length	60.00" (1524 mm)	
W	Outer Width	42.00" (1067 mm)	
H	Overall Height	22.00" (559 mm)	
A	Overflow Height	17.50" (445 mm)	
B	Long Edge to Drain Center	12.00" (305 mm)	
C	Short Edge to Drain Center	30.00" (762 mm)	
D	Drain Shoe Length	14.00" (356 mm)	
E	Deck Height	2.00" (51 mm)	
F	Deck Width	2.00" (51 mm)	
G	Service Access	12.00 x 18.00" (305 x 457 mm)	N/A
I	Floor Cutout for Drain	12.00 x 4.00" (305 x 102 mm)	
J	Interior Dimensions (JW x JL)	25.00 x 41.00" (635 x 1041 mm)	

## NOTE


The overall dimensions are nominal with a tolerance of +0 and -.25" (6mm).  
 Electrical Specifications  
 (Each component requires a separate, dedicated GFCI protected circuit)  
 Motor/Pump 120V 15A 60HZ  
 Heater (optional) 120V 15A 60HZ




Soaking Bathtub

## Key Dimensions


(Center Drain / Right Side Whirlpool Pump shown)




\*Deck width reflects only area indicated on detail.



Side View



End View



NOTE: Drawings not to scale.