




**ADJUSTABLE STYLE 1 1/2" MILWAUKEE STYLE P-TRAP
WITH CLEANOUT PLUG, IPS THREAD ONE END TUBE
PLUMBING PRODUCT SPECIFICATION**



INSTALLATION MEASUREMENTS

PART NO.	INLET OD	OUTLET SLIP JOINT	HEIGHT	LENGTH	Tube
	(A)	(B)	(C)	(D TO E)	GA
397PCDC	1 1/2	1 1/2	5	13 1/4	17
397PC	1 1/2	1 1/2	5	13 1/4	17
397RBDC	1 1/2	1 1/2	5	13 1/4	17
397L16PCDC	1 1/2	1 1/2	5	13 1/4	17

PART # SUFFIX DESIGNATIONS

DC - Die-cast nut PC - Polished finish
L - 12" Utility extension RB - Rough brass finish

* Part #'s provided standard with Keeney's unique Red TPE "leak free technology" washers

DESCRIPTION

Brass adjustable style 1 1/2" p-trap for plumbing fixture.

Constructed of 17 gauge seamless brass & cast brass elbow with 10" brass utility arm extension.

INCLUDES:

- J-bend, elbow, slip nuts, and slip washers
- Seamless brass tube only
- Heavy duty chromium finish
- Factory testing to ensure leak free performance

INDUSTRY APPROVALS

- UPC/IAPMO
- CSA
- Mass Code
- LA Code

Listing of parts approved for specific codes available. See Keeney contact information below.

SPECIFIER APPROVAL

Job Name _____	Date _____
Model _____	Qty _____
Wholesaler _____	
Contractor _____	
Architect _____	

**FOR MORE INFORMATION CALL 1-800-243-0526
OR E-MAIL NCS@UPT.COM**

THE KEENEY MANUFACTURING COMPANY
www.keeneymfg.com

*Keeney Representative
Stamp or Label Here*