

# **Memoirs®**

Freestanding Bath K-8333

#### **Features**

- Integral slotted overflow allows for deep soaking.
- Center toe-tap drain with cast resin material cover.
- Integral lumbar support.
- 17-15/16" soaking depth.
- 66" (1676 mm) x 36" (914 mm) x 24" (610 mm).

#### Material

KOHLER Lithocast®

### Installation

Freestanding.



Codes/Standards CSA B45.5/IAPMO Z124

See website for detailed warranty information.

**Available Color/Finishes** 

Color tiles intended for reference only.

**Color Code Description** 


0 White








Freestanding Bath **K-8333** 





## **Technical Information**

All product dimensions are nominal. Installation: Freestanding

Drain location: Center

Basin area, bottom: 53-7/16" x 23-5/16" (1358 mm x 592 mm)
Basin area, top: 63-9/16" x 33-9/16" (1614 mm x 852 mm)

Weight: 262 lbs (118.8 kg)

Minimum floor load: 112.2 lbs/ft² (547.8 kg/m²)
Water depth: 17-15/16" (455 mm)
Water capacity: 98.74 gal (373.8 L)

Template: Footprint, 1314994, not required, not

included

# **Notes**

Measure your actual product for rough-in details. Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Allow for 3" (76 mm) diameter of clearance around the drain pipe on finished floor material to prevent drain body interference during installation.

