

## **Composed®**

## Single-handle Bathroom Sink Faucet K-73053-4

### **Features**

- Joystick handle allows for both on/off actuation and temperature setting.
- KOHLER ceramic disc valves exceed industry longevity standards over two times for a lifetime of durable performance.
- Temperature memory allows faucet to be turned on and off at any temperature setting.
- Pair with Composed faucets, accessories and showering components to coordinate a full bathroom.
- 1.2 gal/min (4.5 l/min) maximum flow rate [max at 60 psi (4.1 bar)]

#### Material

- Premium metal construction.
- Durable KOHLER finishes resist corrosion and tarnishing.

### Installation

- Flexible supply connections for easy installation.
- Single-hole mounting.
- Not for use on sinks with centerset drillings.
- Tall-height for vessel sink applications.





## ADA CSA B651

Codes/Standards
ASME A112.18.1/CSA B125.1
NSF/ANSI 61
NSF/ANSI 372
All applicable US Federal and State material regulations
DOE - Energy Policy Act 1992

EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651
OBC

## KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### **Available Color/Finishes**

Color tiles intended for reference only.

Color Code Description

CP Polished Chrome


TT Titanium





## **Composed®**

# Single-handle Bathroom Sink Faucet K-73053-4



### **Technical Information**

All product dimensions are nominal.

Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Pressure: 60 psi (4.1 bar)

Valve body: Cast Brass

Drain with overflow: YES
Drain tailpiece YES

included:

Spout:

Spout reach: 7-1/8" (181 mm)

### **Notes**

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

