


Pfirst Series™ Tub And Shower Trim

- R89-0100 Finish(C) LG89-020K Finish(K)
- R89-010K Finish(K) LG89-020Y Finish(Y)
- R89-010Y Finish(Y) LG89-0300 Finish(C)
- LG89-0200 Finish(C) LG89-030K Finish(K)
- LG89-030Y Finish(Y)



Specifications

- Trim Only, Valve Not Included

Features

- 1.8 GPM Shower Head
- Trim Only, Valve Not Included
- Quick Trim Installation- Attaches Without Tools, No Exposed Screws
- Requires OX8 or JX8 Valve Bodies
- Easy to Clean Nozzles
- Tub & Shower (O30* Only)
- Shower Only (O20* Only)
- Handle Trim Only (O10* Only)
- Metal Shower Arm and Flange
- Quick Connect Tub Spout (O30* Only)
- 1.5 GPM Shower Head Low Flow Restrictor Available: Order Part # 941-055 Orange Colored Restrictor Separately
- Pforever Warranty®

Code Compliance

Pfister products are designed and manufactured in compliance with the following standards and codes:

- IAPMO Certified
- CSA B125 Certified
- ASME A112.18.1
- Cal Green Compliant
- CEC Compliant
- EPA WaterSense Certification 1.8 gpm, 6.8 L/Min
- ADA Compliant-ANSI A117.1 (Lever handles only)



Dimensions

