



SPECIFICATIONS

Ideal For


T8 | T12 | Retrofits

Features

- Uses Two 4ft LED Lamps with Quick Connect to Create an 8ft Lamp
- Shatter Proof Acrylic Lens
- Non-Dimmable
- Indoor / Suitable for Damp Locations
- UL/CUL Listed
- FCC Compliant
- 100% Glass and Mercury Free
- 5 Year Warranty
- Cool White

Benefits

- Instant Full Brightness
- Direct Replacement for Fluorescent 8' Lamps
- Eliminates Flicker From T12 Fluorescent Lamps
- Eliminates Humming & Buzzing Associated with T12 Fluorescent Lamps
- 50,000 Hour Rated Life
- Rotating Endcap for Adjusting Light Direction







Specifications

Item Number	Input Power (Watts)	Input Line Voltage	Base Type
T96/841/LED	46	Works off of existing ballast voltage	1-Pin
Lumens	Lumen Efficiency (LPW)	ССТ	MOL
4100	89	4100K	96"
Diameter	Life Hours	Minimum Starting Temperature	•
1"	50,000	-13°F	

LM-79 and LM-80 data available upon request.