



Z415-B


BODY ASSEMBLY W/ "TYPE B" STRAINER and EZ1™ TECHNOLOGY

SPECIFICATION SHEET

TAG _____

**PATENT
PENDING**

Dimensional Data (inches and [mm]) are Subject to Manufacturing Tolerances and Change Without Notice



Note:
Minimum K Dimension is Only
Possible with -LR Option when
using 6" [152] or 8" [203] Strainer

Dimensions In Inches								Approx. Wt. Lbs. [kg]	Strainer Open Area Sq. In [cm ²]
A Pipe Size	B Strainer Dia.	D		K		K'			
		Min.	Max.	Min.	Max.	Min.	Max.		
2-3 [51-79]	5 [127]	0	1-1/4 [32]	1-1/2 [38]	2-23/32 [69]	2-1/32 [51]	3-7/32 [82]	16 [7]	6-1/4 [40]
2-3-4 [51-76-102]	6 [152]	0	1-1/4 [32]	1-1/2 [38]	2-9/16 [65]	1-31/32 [50]	3-5/32 [80]	19 [9]	9 [58]
3-4 [76-102]	8 [203]	0	1-7/32 [31]	1-7/8 [48]	2-29/32 [74]	2-13/32 [61]	3-1/2 [89]	24 [11]	20 [129]
6 [152]	8 [203]	0	1-7/32 [31]	1-7/8 [48]	2-29/32 [74]	2-13/32 [61]	3-1/2 [89]	26 [12]	20 [129]

ENGINEERING SPECIFICATION:

Zurn Z415-B floor and shower drain, Dura-coated cast iron body with bottom outlet, combination invertible membrane clamp and adjustable collar with seepage slots and top assembly. EZ1™ drainage series is engineered to simplify product installation, comprised of concrete shield, up to 1-1/4" [32] of vertical post pour adjustment, pre-packaged shims for tilt correction and integrated, self-contained "Type B" light duty strainer with rough-in cover for protection during concrete pour.

OPTIONS (Check/specify appropriate options)

PIPE SIZE

2-3-4 [51-76-102]
2-3-4 [51-76-102]
2 [51]
3 [76]
4 [102]
6 [152]
2-3-4 [51-76-102]
2-3-4 [51-76-102]

(Specify size/type) OUTLET

_____ IC Inside Caulk
_____ IG Inside Gasket
_____ IP Threaded
_____ IP Threaded
_____ IP Threaded
_____ IP Threaded
_____ NH No-Hub
_____ NL Neo-Loc

'E' BODY HT. DIM.

4-13/16 [122]
4-13/16 [122]
2-7/16 [62]
2-3/4 [70]
2-13/16 [71]
2-7/8 [73]
3-13/16 [97]
3-7/8 [98]

PREFIXES

___ ZB D.C.C.I. Body Assembly w/ Polished Bronze Top
___ ZN D.C.C.I. Body Assembly w/ Polished Nickel Bronze Top*
___ ZS D.C.C.I. Body Assembly w/ Polished Stainless Steel Top

SUFFIXES

___ -AR Acid Resisting Epoxy Coated Cast Iron
___ -EF 3/4 [19] Extension Frame
___ -G Galvanized Cast Iron
___ -LR Low Rough-In (For 6 [152] and 8 [203] Strainers Only)
___ -P Trap Primer Connection (Specify 1/2" [13] or 3/4 [19])
___ -SA Stabilizer Assembly (See Z1035)
___ -SQ Stabilizer Q-Deck (See Z1035-Q)
___ -SR Stabilizer Ring
___ -TC Neo-Loc Test Cap Gasket (2-4 [51-102] NL Outlet Only)
___ -TSP Trap Seal Protection Device (Size Matches Drain Outlet Selected) (See Z1072)
___ -U 2 - 3-1/4 [51-83] High Extension Adapter
___ -VP Vandal-Proof Secured Top
___ -Y Sediment Bucket

* Regularly furnished unless otherwise specified.