



## Z1375 GROUND HYDRANT Encased, Moderate Climate, Interior Use

|--|

TAG \_\_\_\_\_

Dimensional Data (inches and [ mm ]) are Subject to Manufacturing Tolerances and Change Without Notice





**PARTS LIST** 

PRODUCT NO. Z1375

Approx. Wt. Lbs. [kg] 8 [4]

## **ENGINEERING SPECIFICATION: ZURN Z1375**

Encased, moderate climate ground hydrant for flush with grade or finished floor installation. Complete with all bronze interior parts, replaceable bronze seat and seat washer, and non-turning operating coupling with free-floating compression closure valve. Dura-Coated Cast Iron box and scoriated hinged cover with "WATER" cast on cover.

**OPTIONS** (Check/specify appropriate options)

\*WHEN ORDERING REPLACEMENT PARTS SPECIFY Y DIM.

3/4 [19] OR 1 [25] FEMALE I.P.S.

			<u>ltem</u>	<u>Name</u>	Quan.
SUFFIXES			3	Operating Screw	1
DP14	1/4 [6] IP Drain Port in Box		<u>4</u>	O-Ring	<u>1</u>
HD	Heavy Duty Cover (Cast Iron and -NB only)		<u>5</u>	Operating Coupling	<u>1</u>
NB	Polished Nickel Bronze Face		<u>6</u>	Washer Guide	<u>1</u>
PB	Polished Bronze Face		<u>7</u>	Washer	1
-RK	Hydrant Parts Repair Kit		8	<u>Screw</u>	1
-VB	3/4 [19] Adapter Vacuum Breaker		<u>16</u>	Removable Seat	<u>1</u>
	(Requires deeper box to accommodate				
	vacuum breaker.)				
		REV. G	DATI	E: 04/06/11 C.N. NO. 12 <sup>-</sup>	1131

DWG. NO. 58881