

NIBCO® Press System Tools

PC-280 & PC-20M FEATURES

TOOLS

Light weight

- PC-20M Mini: 3.7 lbs. (without jaw)
- PC-280: 9.4 lbs. (without jaw)

Easy to handle / simple design

- Jaws rotate 350°
- No calibration necessary
- No complicated switches or controls
- Mini: Ergonomic compact design is easy to use in tight spaces

Interruptible crimp cycle

- Safety feature prevents injuries
- Can begin crimp, stop to align and level fitting / tube, and complete crimp

Battery

- Can be changed during crimp cycle
- Lithium-ion has short charging cycle and larger capacity
- PC-4ML: 15 minute recharge time
- PC-7L: 22 minute recharge time

AC Power Adapter

- Converts the tool to electric power
- Allows continuous use

Service light

- Illuminates at 10,000 cycles
- Tool will not stop operating when light illuminates
- RED indicates battery charge status, service intervals, tool functions & faults
- WHITE illuminates the work area

Hydraulic Pressure Check (HPC)

- An audible warning signal sounds if adequate working pressure is not achieved

PRESSING CHAINS (2 1/2" to 4" ONLY)

Uniform crimp

- Maintains proper pipe alignment

Easy to install and remove

- Once secured to fitting, chain cannot fall off prior to crimp
- Chain easily removed post crimp

Crimp Identification

- Easy to identify crimp has been made from a distance

PC-100 and PC-10M Accessories

MATERIAL LIST

MODEL NO.	DESCRIPTION	LBS.
PC-7	12V, NiMH Battery - 3.0Ah for PC-100	1.57
PC-8	120V Standard Battery Charger for PC-6 or PC-7	1.10
PC-4M	1.3 Ah NiCd 9.6V Battery for Mini Pressing Tool	0.85
PC-5M	120V Charger for Mini Pressing Tool	1.13
PC-100C	Metal Case for PC-100 Tool	14.30



PC-4M

9.6V, 1.3 Ah
NiMH Battery



PC-7

12V, 3.0 Ah
NiMH Battery



PC-8

120V Battery Charger