60 x 34 x 84

#### **TUB-SHOWER MODEL #60ACTS**



## **FEATURES**

- Decorative back wall
- Slip resistant, textured bottom
- Premium cast acrylic surface
- Face pack
- Limited 5-year warranty

# **OPTIONS**

- Designer drain waste & overflow: Bone, Brushed Nickel, Polished Brass, Polished Chrome, Oil-Rubbed Bronze, Polished Brass
- Dome light
- Shower door series: LO516

# **AQUATIC ADVANTAGE**

- National distribution
- 6 manufacturing facilities
- Private fleet
- Centralized customer service
- Field support

#### **COLOR & TRIM OPTIONS**


Stock	Premium		
Biscuit White	Black Sterling Silver		











FEATURES lbs Dimensional Tolerance ± 3/8". Dimensions needed for site preparation should be measured from the unit. Aquatic assumes no responsibility for preparatory work.


Type and Moo	del # Materia	al Wall Finish	Pieces	Drain	Seats	Lights	Pkg. Wt.
Tub-Shower #60	OACTS Cast Acr	ylic Decorative back v	wall 1	LH or RH	_	Optional	175

### **DIMENSIONS**

Specifications	inches
Width: Overall / Net	60
Depth: Overall / Net	34 / 34
Height: Overall / Net	84
Enclosure Opening	51 <b>%</b> W×62 <b>%</b> H
Skirt Height	16 1/2
Drain Rough-In (from Back Wall)	17 1/2
Drain Rough-In (from Side Wall)	] 3/4
Drain: Diameter / Clearance	2 / 2 3/4

#### FRAMING DIMENSIONS inches

Туре	<b>D</b> Depth	<b>W</b> Width	H Height	<b>A</b> Box-Out	В	С
Alcove	35	60 1/8	-	6 x 12	1 3⁄4	17 1/2



### SUMP DATA

Top of Drain to	Capacity	Min. Operating	WIDTH @ centerline		DEPTH @ centerline	
Bottom of Overflow	to Overflow gal	Capacity — gal	Тор	Bottom	Тор	Bottom
9	34.7	=	56 ½	44 %	24 1/8	22 1/4