# DARSEY 10242 - DARSEY BATH & SHOWER SUITES

#### 102 x 42 x 78 3/4 inches

#### SOAKER MODEL #102422P WHIRLPOOL MODEL #102422PWP



### AQUATIC ADVANTAGE

- National distribution
- 6 manufacturing facilities
- Private fleet
- Centralized customer service
- Field support

### COLOR OPTIONS

Stock	Upgraded	Premium
White	Almond Linen/Biscuit Bone	Black Mexican Sand Sand Bar Sterling Silver

## **FEATURES**

- 2-piece tub & shower suite
- 42" x 42" shower with integral toiletry shelf
- 60" x 42" bathtub with oval sump, pony wall, 2-sided wainscot and integral skirt
- Textured tile
- Molded toiletry shelves
- 8" wainscot
- Right or left hand tub location
- Ergonomic backrest
- Slip-resistant, textured bottom
- AcrylX<sup>™</sup> applied acrylic surface
- Lifetime limited warranty

#### Whirlpool Features:

- 6 directional hydrotherapy jets
- Color matched trim (select colors)
- Pneumatic on/off control
- Advanced safety suction system

## OPTIONS

- Removable access panel (whirlpool models)
- Designer drain, waste & overflow
- Shower Door Series L051






# DARSEY 10242

102 x 42 x 78 3/4 inches





414

31

FEATURES Dimensional Tolerance ± %". Dimensions needed for site preparation should be measured from the unit. Aquatic assumes no responsibility for preparatory work.

Model #	Material	Wall Finish	Jets	Motor	Controls	Drain	Net Wt. Ibs	Pkg. Wt. Ibs
Soaker #102422P	AcrylX™	Textured Tile	0	-	-	LH or RH	190	200
Whirlpool #102422PWP	АсгуIХ™	Textured Tile	6	63 GPM	Pneumatic	LH or RH	240	250

#### DIMENSIONS


Δ

6"

Specifications	inches			
Width: Overall / Net	102			
Depth: Overall / Net	43 ¼ / 42			
Height: Overall / Net	80 / 78 <b>¾</b>			
Enclosure Opening	_			
Skirt Height	17 ½			
Drain Rough-In (from Back Wall)	21 <b>¾</b> tub / 21 shower			
Drain Rough-In (from Side Wall)	3 ¼ tub / 21 shower			
Drain: Diameter / Clearance	2 / 1/2			

#### FRAMING DIMENSIONS inches

Туре	<b>D</b> Depth	<b>W</b> Width	<b>H</b> Height	А	<b>B</b> Tub/Shower	<b>C</b> Tub/Shower
Alcove	43 ¼	102	80	Box Out	3 1/4 / 21	21 3/4 / 21



#### SUMP DATA

Top of Drain to	Capacity Min. Operating		WIDTH @ centerline		DEPTH @ centerline	
Bottom of Overflow	to Overflow gal	Capacity — gal	Тор	Bottom	Тор	Bottom
12 1/ <b>8</b>	67	50	51 1 <b>⁄8</b>	4] <b>5%</b>	34 ½	29