


1483TSTH – ACCESSIBLE SHOWERS

inches

Interior: 46 x 34 1/4 x 75

Exterior: 48 x 36 1/4 x 76 1/2



AQUATIC ADVANTAGE

- National distribution
- 6 manufacturing facilities
- Private fleet
- Centralized customer service
- Field support

COLOR & TRIM OPTIONS

Stock	Upgraded
White	Almond Biscuit Bone

**Additional custom colors available.
(Contact Customer Service)

FEATURES

- AcrylX™ applied acrylic surface
- 2 1/2" (65 mm) skirt
- 1 1/2" (40 mm) interior threshold
- Smooth tile
- Center drain
- Molded seat (LH or RH)
- Molded toiletry shelves
- Lifetime limited warranty (30 year commercial)

OPTIONS

- LH or RH fixture wall
- Grab bars
- Hand-held shower assembly with slide bar
- Pressure balancing mixing valve
- Curtain rod and/or shower curtain

CODE COMPLIANCE

- IAPMO Z124-2011

**Code compliant when fully equipped and installed according to guidelines.




Aquatic products may be specified as Lasco Bathware.



1483TSTH

Interior: 46 x 34 1/4 x 75
Exterior: 48 x 36 1/4 x 76 1/2
inches



FEATURES

Dimensional Tolerance $\pm \frac{3}{16}$ ". Dimensions needed for site preparation should be measured from the unit. Aquatic assumes no responsibility for preparatory work.

Type and Model #	Material	Wall Finish	Pieces	Drain	Dam/Skirt Height	Net Wt. lbs	Pkg. Wt. lbs
Shower #1483TSTH	AcrylX™	Smooth tile	1	Center	2 1/2" (65mm) skirt	110	120

DIMENSIONS

Specifications	inches
Width: Overall / Net	48 / 46
Depth: Overall / Net	36 1/4 / 34 1/4
Height: Overall / Net	76 1/2 / 75
Enclosure Opening:	46
Skirt Height:	2 1/2
Drain Rough-In (from Back Wall)	16
Drain Rough-In (from Side Wall)	24

FRAMING DIMENSIONS inches

Type	D Depth	W Width	H Height	A	B	C
Alcove	36 1/4	48 1/8	—	Box Out	24	16

