
# 3636BFS - ACCESSIBLE SHOWERS

inches

Interior: 36 x 36 x 80 7/16 Exterior: 41 x 37 x 83 3/4



### AQUATIC ADVANTAGE

- National distribution
- 6 manufacturing facilities
- Private fleet
- Centralized customer service
- Field support

#### COLOR & TRIM OPTIONS

Stock	Upgraded
White	Biscuit

\* \*Additional custom colors available. (Contact Customer Service)

## **FEATURES**

- Premium cast acrylic surface
- 1 ¾″ skirt
- ½" interior threshold
- Barrier free when properly installed
- Smooth wall
- Center drain
- Molded toiletry shelf
- Integral dome
- 5-year limited warranty

### **OPTIONS**

- RH or LH fixture wall
- Grab bars
- Fold-up seat
- Hand-held shower assembly with slide bar
- Pressure balancing mixing valve
- Soap dish
- Curtain rod and/ or shower curtain
- Dome light

### CODE COMPLIANCE

- ADA
- FHA
- ICC/ANSI A117.1
- IAPMO Z124-2011
- HUD UM73a
- CAN/CSA-B651-04
- CSA-B45-11
  - \*\*Code compliant when fully equipped and installed according to guidelines.




Aquatic products may be specified as Lasco Bathware.





Aquatic products may be specified as Lasco Bathware.

3636BFS



FEATURES Dimensional Tolerance ± %". Dimensions needed for site preparation should be measured from the unit. Aquatic assumes no responsibility for preparatory work.

Туре

Type and Model #	Material	Wall Finish	Pieces	Drain	Dam/Skirt Height	Net Wt. Ibs	Pkg. Wt.	
Shower #3636BFS	Cast Acrylic	Smooth	1	Center	1 $\%''$ skirt, $\%''$ interior threshold	172	182	

#### DIMENSIONS

Specifications	inches
Width: Overall / Net	41 / 36
Depth: Overall / Net	37 / 36
Height: Overall / Net	83 ¾ / 80 7⁄16
Enclosure Opening:	36
Skirt Height:	] 3⁄4
Drain Rough-In (from Back Wall)	19
Drain Rough-In (from Side Wall)	20 <b>½</b>

#### FRAMING DIMENSIONS inches

