

TAG

-ø12 |305| [51] 2 Д

Dimensional Data (inches and [mm]) are Subject to Manufacturing Tolerances and Change Without Notice

	· ·
V	
$\langle \rangle$	

A	Approx. Wt. Lbs.	Grate Open
Pipe Size In.[mm] Wt. Lb		Area
	[kg]	Sq. In. [cm ²]
2, 3, 4 [51, 76, 102]	21 [10]	10 [116]
6 [152]	25 [11]	18 [116]

ENGINEERING SPECIFICATION: ZURN Z508

9" [229mm] Diameter top drain, Dura-Coated cast iron body with bottom outlet, seepage pan and combination membrane flashing clamp and frame for extra-heavy-duty cast iron deep flange slotted grate.

OPTIONS (Check/specify appropriate options)

PIPE SIZE 4 [102] 4 [102] 4 [102] 2, 3, 4 [51, 76, 102]	(Specify size/type) OUTLET IC Inside Caulk IG Inside Gasket IP Threaded NH No-Hub	'E' BODY HT. DIM. 3-3/4 [95] 3-3/4 [95] 2-3/4 [70] 4-3/4 [121]
6 [152] 2, 3, 4 [51, 76, 102]	International NH No-Hub	5-1/4 [133] 3-9/16 [90]
DDEEIVES		

PREFIXES

- D.C.C.I. Body and Top* Ζ
 - D.C.C.I. Body with Polished Bronze Top (Add 3/16 [5] to 2 [51] Dim. and 3/4 [20] to 9 [229] Dim.) ZΒ
 - ΖN D.C.C.I. Body with Polished Nickel Bronze Top (Add 3/16 [5] to 2 [51] Dim. and 3/4 [20] to 9 [229] Dim.)

SUFFIXES

AR	Acid Resisting Epoxy Coated Cast Iron	TC	Neo-Loc Test Cap Gasket
DG	Duresist Grate		(2, 3, 4 [51, 76, 102] NL Bottom Outlet Only)
G	Galvanized Cast Iron	TS	Top Secured with Slotted Screws
HP	Heel-Proof Grate	VP	Vandal-Proof Secured Top
P	Trap Primer Connection	Y	Sediment Bucket
S	Secondary Strainer	90	90º Threaded Side Outlet Body
SC	Solid Cover with Lift Handle		(4 [102] Size Only)
SG	Solid Gasketed Cover with Lift Handle		

* Regularly furnished unless otherwise specified.