TSURUMI PUMP Portable Generators

TPG4 SERIES GENERATORS SPECIFICATIONS

TSURUMI TPG4 Series Generators are designed to withstand the severe conditions of construction jobsites or industrial applications, especially where extra durability and dependable, stable power are required. Ideal to supply the power to Tsurumi's single-phase submersible pumps and all your electrical power tools such as drills, saws, lighting and heaters.

TPG4 Series Generators Features powered by Honda

- · High Capacity Fuel Tank with Fuel Gauge for extended run time.
- Large, Silent Muffler with USDA qualified spark arrestor to greatly reduce noise.
- Optional Wheel Kits & Lifting Bail are available.
 (PGWK-200X as Wheel Kits and PGLB-1X as Lifting Bail)



	TPG4-3000HDX	TPG4-4500HDX
Max. / Rated Output (watts)	2600 / 2200	4500 / 3600
Max. / Rated Current (120V / 240V)	23.3 / 18.3	37.5/30, 18.7/15
Voltage (V) (60Hz)	120	120 / 240
AC Outlet Replacement	1-NEMA 5-20R Duplex (20A, 12A, W/GFCI)	2-NEMA 5-20A Duplex (20A, 12A, W/GFCI) 1-NEMA L5-30R (30A, 120V, Twist Lock) 1-NEMA L14-30R (30A, 120/240V, Twist Lock)
Engine Model	GX160T2	GX240T2
Maximum HP	5.5 (3600RPM)	8.0 (3600RPM)
Displacement	163 (10inch ³)	242 (15inch ³)
Fuel Tank Capacity (gallon)	4.2	6.6
Running Time (Rated load)	12.1	12.5
Starting System	Recoil	Recoil
Noise Level (Rated Load)	64dB	68dB
Shipping Size (LxWxH) (inches)	24.4 x 19.5 x 20.5	27.6 x 23.4 x 22.6
Shipping Weight (lbs.)	110	161

	TPG4-6000HDX	TPG4-7000HDX TPG4-7000HDXE
Max. / Rated Output (watts)	5500 / 4800	6800 / 6000
Max. / Rated Current (120V / 240V)	45.8/40, 22.9/20	56.7/50, 28.3/25
Voltage (V) (60Hz)	120 / 240	120 / 240
AC Outlet Replacement	2-NEMA 5-20A Duplex (20A, 12A, W/GFCI) 1-NEMA L5-30R (30A, 120V, Twist Lock) 1-NEMA L14-30R (30A, 120/240V, Twist Lock)	
Engine Model	GX340T2	GX390T2
Maximum HP	11.0 (3600RPM)	13.0 (3600RPM)
Displacement	337 (21 inch ³)	389 (24inch ³)
Fuel Tank Capacity (gallon)	6.6	6.6
Running Time (Rated load)	8.5	7.6
Starting System	Recoil	Recoil (HDX), Electric (HDXE)
Noise Level (Rated Load)	72dB	78dB
Shipping Size (LxWxH) (inches)	27.6 x 23.4 x 22.6	27.6 x 23.4 x 22.6
Shipping Weight (lbs.)	183	192(HDX), 199(HDXE)