

Dial Type Thermometers

- Economical
- Back mount

Dual Scale:

- 40°-250°F, 0,-120°C, Accuracy to 1°
- 5° Increments
- 2-1/2" Face
- Brass wells
- Choice of adapters
- Thermometer can be removed from adapter for easy installation

Thermometers supplied complete with connection



Compliant

AB 1953

PART NUMBER	CONNECTION
1449	1/2" MPT
1449-C	Well ONLY



Compliant

AB 1953


PART NUMBER	CONNECTION
1450	3/4" CWT Solder
1450-W	Well ONLY

Dial Type Thermometers

- Superior quality
- Back or bottom mount

Dual scale:

- 32°-250°F, 0°-120°C
- 3-1/2" diameter
- 1/2" MPT brass connection
- 2-1/2" brass element (beyond MPT)
- Corrosion resistant steel case



PART NUMBER	CONNECTION
1455	1/2" MPT CBM
1457	1/2" MPT Bottom

Spring Strap-On Surface Thermometer

New!

This new thermometer is specifically designed to provide an economical and accurate surface temperature measurement on any 1/2" to 4" pipe: iron, plastic, steel or copper. Easy on, easy off!

- Dual Scale
40°C/240°F
0°C/120°C
- 5° increments
- Acrylic lens
- Accuracy +/- 3°



PART NUMBER	CONNECTION
1446	4 Stainless Steel Springs