

Perlator®

Faucet Aerator - 1.8 gpm

Flow Restricted Regular Size



Features and Benefits

- ▶ Watercolours® design: Color coding to identify flow rate and stream pattern.
- ▶ Patented construction provides asplash-free stream, well-aerated and soft to the touch.
- ▶ Integrated anti-liming honeycomb replaces conventional wire mesh screens prone to lime build up.
- ▶ Anti-clogging dome screen filters sediment and particles.
- ▶ Compatible with regular and vandal proof M22 & M24 metric housings.
- ▶ Available housing finishes: chrome, polished brass, brushed nickel and oil rubbed bronze.
- ▶ Laser marked housings with statutory marks.

Certifications

ANSI/NSF®-61-372
ASME A112.18.1M and CSA B125
Meets **CALGreen** requirements

Thread & Part Number

Part #	Designation	Thread Size
11 635	Insert only	
11 600	Regular male	15/16"-27
11 610	Regular female	55/64"-27
11 620	Regular dual thread	15/16"-27 x 55/64"-27
11 604	Vandal proof regular male	15/16"-27
11 614	Vandal proof regular female	55/64"-27
11 626	Vandal proof regular dual thread	15/16"-27 x 55/64"-27

Other product combinations available.




Packaging:

Inserts *1 pc (bag), 6 pcs (tube), 50 pcs (bag)*
Reg. male/female/dual thread *1 pc (bag), 6 pcs (tube), 50 pcs (tray)*
Reg. vandal proof male/female/dual thread *1 pc (bag), 6 pcs (tube), 40 pcs (tray)*

Color Code

Dome	Ring	Basket
Brown	Natural	Dark Gray

Flow Rate Curve



Dimensions

No	mm	In
A	20.88	.822
B	12.00	.472
C	19.97	.786
D	≈ 13	≈ 1/2


Housings



Technical Data

Materials: Body Acetal
O-ring EPDM
Washer EPDM

Continuous



Short-term (5 minutes max.) Per ASME A112.18.1 testing requirements.

