NEWPORT BRASS

CHESTERFIELD

Features

- Solid brass construction
- Bridge-style brass valve bodies
- Quarter-turn washerless ceramic disc valve cartridges
- ADA compliant traditional lever handles
- Swivel spout assembly
- 6-3/8" (16.2 cm) spout height at outlet
- 9-7/16" (24.0 cm) spout reach (c-c)
- For 8" (20.3 cm) centers
- 1.8 gallons (6.8 liters) per minute maximum flow rate

Codes / Standards Compliance

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- NSF 61
- ADA
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations

Bridge Style Kitchen Faucet







Colors / Finishes

- 10B: Oil Rubbed Bronze
- 15: Polished Nickel
- 15S: Satin Nickel PVD
- 26: Polished Chrome

• Other: Refer to the Newport Brass catalog for additional color/finish options.


Specified Model		
Model	Description	Colors Finishes
9461	Bridge Style Kitchen Faucet	☐ 10B ☐ 15 ☐ 15S ☐ 26 ☐ Other

Product Specification: Add "Color / Finish" suffix to Model number, below.

The Bridge Style Kitchen Faucet shall be made of solid brass construction. Faucet shall incorporate a swivel spout assembly and feature bridge-style brass valve bodies with quarter-turn washerless ceramic disc valve cartridges. Faucet shall have a 1.8 gallons (6.8 liters) per minute maximum flow rate. Product shall be for 8" (20.3 cm) centers. Product shall incorporate a 6-3/8" (16.2 cm) spout height at outlet and a 9-7/16" (24.0 cm) spout reach (c-c). Faucet shall incorporate ADA compliant traditional lever handles. Bridge-Style Kitchen Faucet shall be Newport Brass Model 9461/_____.

9461

PRODUCT DIMENSIONS (Units are in inches)



Chesterfield Bridge Style Kitchen Faucet with Sidespray **9461**



t: 949.417.5207 | www.newportbrass.com ©2015 Brasstech, Inc.

Page 2 of 2 Spec_9461