NEWPORT BRASS

NEWPORT BATH

Features

- Solid brass construction
- Traditional styling
- Single function spray
- Rubber nozzles facilitate easy cleaning
- Ball and socket design having a range of 60 degrees
- 1/2" NPSM inlet fitting
- 2-3/4" (7.0 cm) Body Spray diameter
- 1.8 gallons (6.7 liters) per minute maximum flow rate

Codes / Standards Compliance

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations

Colors / Finishes

- 10B: Oil Rubbed Bronze
- 15: Polished Nickel
- 15S: Satin Nickel PVD
- 26: Polished Chrome
- Other: Refer to the Newport Brass catalog for additional color/finish options.

Specified Model		
Model	Description	Colors Finishes
2170	Body Spray	10B 15 15S 26 Other

Product Specification: Add size designator and "Color / Finish" suffix to Model number, below.


The Body Spray shall be of solid brass construction. Body Spray shall have a single function spray pattern incorporating rubber nozzles to facilitate easy cleaning. Body spray shall have a 1/2" NPSM inlet fitting and 2-3/4" (7.0 cm) diameter while operating at 1.8 gallons (6.7 liters) per minute maximum flow rate. Body Spray shall be Newport Brass Model 2170/____.




Body Spray

2170

PRODUCT DIMENSIONS (Units are in inches)





Newport Bath Body Spray 2170



t: 949.417.5207 | www.newportbrass.com ©2014 Brasstech, Inc.

Page 2 of 2 Spec_2170_c_7.18