

NEWPORT 365

Features

Widespread Lavatory Faucet

- Solid brass construction
- · Brass valve bodies
- Quarter-turn washerless ceramic disc valve cartridges
- Specified handles (lever or cross) are ADA compliant when used with Widespread Lavatory Faucet
- Spout assembly with integral supply hoses
- Pop-up drain with tailpiece
- 3-7/8" (9.8 cm) spout height at outlet
- 6-15/16" (17.6 cm) spout reach (c-c)
- For 8" (20.3 cm) centers Maximum 20" (50.8 cm)
- 1.2 gallons (4.5 liters) per minute maximum flow rate





2-222

Codes / Standards Compliance

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- NSF 61
- ADA
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations
- EPA Watersense

Colors / Finishes

• 10B: Oil Rubbed Bronze Polished Nickel • 15S: Satin Nickel - PVD Polished Chrome • 26:

• Other: Refer to the Newport Brass catalog for additional color/finish options.

Specified Model		
Model	Description	Colors Finishes
7300	Widespread Lavatory Faucet	☐ 10B ☐ 15 ☐ 15S ☐ 26 ☐ Other
2-116	Lever Handles	☐ 10B ☐ 15 ☐ 15S ☐ 26 ☐ Other
2-222	Cross Handles	☐ 10B ☐ 15 ☐ 15S ☐ 26 ☐ Other

Product Specification: Add "Color / Finish" suffix to Model number, below.

The two-handle Widespread Lavatory Faucet shall be made of solid brass construction. Faucet shall incorporate a spout assembly with integral supply hoses and feature brass valve bodies with quarter-turn washerless ceramic disc valve cartridges. Faucet shall have a 1.2 gallon (4.5 liter) per minute maximum flow rate. Product shall be for 8" (20.3 cm) centers - Maximum 20" (50.8 cm). Product shall incorporate a 3-7/8" (9.8 cm) spout height at outlet and a 6-15/16" (17.6 cm) spout reach (c-c). Widespread Lavatory Faucet shall be Newport Brass Model 7300/____. Handle shall be 2-___/___.

7300

PRODUCT DIMENSIONS (Units are in inches)



