

# **NEWPORT BATH**

#### **Features**

- Solid brass construction
- Traditional styling
- Single function spray
- Rubber nozzles facilitate easy cleaning
- Ball and socket design having a range of 60 degrees
- 1/2" NPSM inlet fitting
- 2-1/2" (6.4 cm) Body Spray diameter
- 1.8 gallons (6.7 liters) per minute maximum flow rate

### **Codes / Standards Compliance**

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations

#### **Colors / Finishes**

10B: Oil Rubbed Bronze15: Polished Nickel

• 15S: Satin Nickel - PVD

• 26: Polished Chrome

• Other: Refer to the Newport Brass catalog for additional color/finish options.



2178





Specified Model		
Model	Description	Colors   Finishes
2178	Body Spray	☐ 10B ☐ 15 ☐ 15S ☐ 26 ☐ Other

### Product Specification: Add size designator and "Color / Finish" suffix to Model number, below.

The Body Spray shall be of solid brass construction. Body Spray shall have a single function spray pattern incorporating rubber nozzles to facilitate easy cleaning. Body spray shall have a 1/2" NPSM inlet fitting and 2-1/2" (6.4 cm) diameter while operating at 1.75 gallons (6.6 liters) per minute maximum flow rate. Body Spray shall be Newport Brass Model  $2178/\_\_$ .

# 2178

## **PRODUCT DIMENSIONS** (Units are in inches)



