

## TF4-099 / TF5-099 MR. COFFEE® 4-CUP COFFEEMAKER



TF5-099

1 Covered Water Reservoir with Easy-to-Read Instructions 2 Dishwasher-Safe Brew Basket 3 Easy-View Water Window 4 Pause 'n Serve 5 4-Cup Easy-Pour Glass Carafe 6 Non-Stick Warming Plate 7 Heavy duty On/Off LED Switch

## **PRODUCT HIGHLIGHTS**

- · Pause 'n Serve feature allows guests to get coffee during brew process
- · Flavor seal carafe lid preserves freshness
- · Easy-pour glass carafe with convenient cup markings and easy-grip handle
- Non-stick warming plate
- · Covered water reservoir with printed instructions
- · Easy-view water window
- · Dishwasher-safe brew basket
- · Complies with NEW UL1082 Hospitality standard
- 1-hour auto-off
- · Two Year Limited Hospitality Warranty

Specifications	
Capacity	4 Cups
Brew Basket	Permanent, lift up, flat filter
Rated Power	120V, 60Hz, 650W
AMPs	5.4 Amps
Power Cord	36", 3 Prong
Approvals	ETL - 1082 Hospitality
Brew Temp	185°F - 210°F
Holding Temp	175°F - 190°F
Max. Brew Time	5 minutes
Auto Shut-off	60 min - +/- 15 min.
Product Dimensions	9.75"x7"x 6.3" (H/L/W)
Product Weight	2.7 lbs
Packaging Dimensions & Weight	7.09"x8.86"x10.24"(H/L/W); 3.09 lbs; .37 cft
Case Qty	4
Case Dimensions	21.26" x 14.76" x 9.25" (H/L/W)
Case Weight	15.4 lbs
Case Cube	1.68 cft
Product UPC	072179230755 (TF4-099) 072179230748 (TF5-099)
Accessories	TF5GCU-099 4-Cup Universal Glass Carafe (Blk); TFSSCU- 099 4-Cup Universal Stainless Carafe (Blk)
Replacement Parts	147464-000-000 Universal Glass Carafe Lid (Wh); 147465 000-000 Universal Glass Carafe Lid (Blk); 147466-000- 000 Universal Stainless Carafe Lid (Blk); 134025-000-000 Brew Basket (Blk)