## **MARS Side Open Disconnect Boxes with Internal Surge**

MARS Disconnect with integrated surge protector provides a unitized design for quick and clean installation. The metal weather-resistant enclosure provides additional robustness and security. MARS Surge Protectors provide the performance necessary to protect critical components in high efficiency mini-split and unitary HVAC equipment.

#### Features:

- · Side open disconnect
- · Integrated internal surge protector
- · Thermally Protected MOV's
- · Metal-weather resistant enclosure
- External Green & Red LED Status Indicators
- cULus rating

MARS NO. 83914

- 3 Year Warranty
- · \$7,500 Connected Equipment Warranty

#### **Specifications Disconnect:**

- · Single phase 240V
- 10,000 Amp rating
- NEMA 3R enclosure
- · Weather proof enclosure
- Available in fused and non-fused

## Surge Protector Ratings:

- 120/240V Single (Split) Phase 50/60Hz
- Short Circuit Current Rating
  22,000 Amps
- MCOV L-N 150V / L-L 330V
- Voltage Protection Rating
  L-N 800V / L-L 1200V
- UL 1449 4th Edition
- Type 1 or 2 Surge Protection Rating

### Protects:

- Compressors
- Heat Pumps
- Ideal for Ductless System
- · Inverter Boards
- ECM Motors
- Control Boards
- Transformers
- Relays
- Sensors



| MARS<br>NO. | DESCRIPTION      | VOLTAGE  | WIRE CONFIGURATION | SPD<br>TYPE | MCOV    | ENCLOSURE          | UL 1449<br>4TH EDITION |
|-------------|------------------|----------|--------------------|-------------|---------|--------------------|------------------------|
| 83915       | 60 Amp Non-Fused | 120/240  | L1,L2,L/N-G        | 1 or 2      | 150/300 | NEMA 3R, Rainproof | cULus                  |
| 83916       | 30 Amp Fused     | 120/240V | L1,L2,L/N-G        | 1 or 2      | 150/300 | NEMA 3R, Rainproof | cULus                  |
| 83917       | 60 Amp Fused     | 120/240V | L1,L2,L/N-G        | 1 or 2      | 150/300 | NEMA 3R, Rainproof | cULus                  |

Replacement Surge Module

# **MARS HVAC Surge Protective Device**

The MARS SPD is designed to protect your HVAC equipment from power spikes, surges and transients. Power spikes and surges can damage compressors, control boards, sensors and ECM motors resulting in costly repairs and down time. The MARS SPD utilizes Thermally Protected MOV technology to provide safe and reliable surge protection.

## Protects:

- Compressors ECM Motors
- Heat Pumps
  Control Boards
- Ideal for
  Ductless Systems
  Relays
- Inverter Boards
  Sensors

# Features:

- Easy Installation to Disconnect
- Weatherproof 4X Enclosure
- 18" Pre-stripped Leads
- · Green & Red LED Status Indicators
- Thermally Protected MOVs
- 120/240V Single (Split) Phase 50/60Hz
- Short Circuit Current Rating
  22,000 Amps
- MCOV L-N 150V / L-L 330V
- Voltage Protection Rating
  L-N 800V / L-L 1200V
- · UL 1449 4th Edition
- · Type 1 or 2 Surge Protection Rating

L1,L2,L/N-G

- · 3 Year Warranty
- \$7,500 Connected Equipment Warranty

120/240



MOV surge technology

ENCLOSURE

Type 4X

cULus

MCOV

150/300

1 or 2

# **MARS HVAC Surge Protective Device**

The MARS 83904 SPD is designed specifically for 120V furnace and air handler applications. The furnace and air handler contain components that must be protected from surges such as, ECM motors, Control Boards, Transformers. The MARS Surge utilizes thermally protected MOV technology for safe and reliable protection of equipment. The 120V Surge Device is easy to install with only 2 wires to connect.

#### Protects:

- Ideal for 120V Ductless Systems
- Furnace & Air Handlers
- Inverter Boards
- ECM Motors
- Control Boards
- Transformers
- Relays
- Sensors

# Features:

- Easy 2 Wire Installation
- 10" Pre-stripped Leads
- · Green LED Status Indicator
- Thermally Protected MOVs
- 120V Single Phase 50/60Hz
- Short Circuit Current Rating
  10,000 Amps
- MCOV L-N 150V
- Voltage Protection Rating
  I -N 700V
- UL 1449 4th Edition
- Type 1 or 2 Surge Protection Rating
- · 3 Year Warranty
- \$7,500 Connected Equipment Warranty



| MARS<br>NO. | VOLTAGE | WIRE<br>CONFIGURATION | SPD<br>TYPE | MCOV | ENCLOSURE | UL 1449<br>4TH EDITION |
|-------------|---------|-----------------------|-------------|------|-----------|------------------------|
| 83904       | 120     | L1,L2,L/N-G           | 1 or 2      | 150  | Type 2    | cULus                  |



83905