

Artifacts® Single-function Showerhead K-72774-G

Features

- Katalyst® air-induction technology maximizes the air/water mix for a powerful, even flow.
- Optimized sprayface for maximum performance.
- MasterClean[™] sprayface prohibits mineral buildup for easy cleaning.
- 1/2" NPT connection.
- Single-function showerhead with 48 nozzle 5-1/2" (140 mm) diameter sprayface.
- 1.75 gal/min (6.6 l/min) maximum flow rate.
- Showerarm and flange not included.
- Coordinates with other products in the Artifacts collection.

Installation

Wall-mount

Water Conservation & Rebates

- WaterSense®-labeled 1.75-gpm showerheads use up to 30 percent less water than standard 2.5-gpm showerheads, while still meeting strict performance guidelines.
- This product can help a building earn Water Efficiency points in the LEED® Green Building Rating System.

Recommended Accessories

K-72775 Shower Arm and Flange



Codes/Standards

ASME A112.18.1/CSA B125.1 DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC)

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes


Color tiles intended for reference only.


Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	2BZ	Oil-Rubbed Bronze





Artifacts® Single-function Showerhead K-72774-G





Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum flow: 1.75 gal/min (6.6 l/min)

Pressure: 80 psi (5.5 bar)

Notes

For use with automatic compensating valves rated at 1.4 gal/min (5.3 l/min) or less.

Install this product according to the installation instructions.

