

Jerritt Series

High-Efficiency Two Piece Toilet



Product Features

- Gravity fed 1.28gpf HET, High Efficiency Toilet
- Two-piece vitreous china
- 2" fully glazed trapway
- 6" x 5-1/4" (RF) / 7" x 6" (EL) water surface
- Anti-siphon fill valve
- Jetted box rim
- Close coupled tank with cover
- Quick connect, 2 bolt tank to bowl installation
- Comes standard with a color matching trip lever
- 2" Flush valve
- Sanitary bar on all bowls
- Seat and supply not included
- Available in 10", 12", 14" RI
- Available with RH trip level
- Available with insulated tank
- Available in round front, elongated, chair height elongated and ADA elongated
- Uses 20% less water than standard low consumption toilets
- EPA WaterSense Certified



PF1403TWH/PF5112HEWH

Codes and Standards

- IAPMO/UPC
- ASME A112.19.2
- CSA B45.0
- CSA B45.1

| Model | Model Description | Color Finishes |
|---|--|-------------------|
| *PF1400T | 1.1-1.6 RF UNIV BOWL | ○ White |
| *PF1401T | 1.1-1.6 EL UNIV BOWL | ○ White ○ Biscuit |
| PF1402T  | 1.1-1.6 CH EL UNIV BOWL | ○ White |
| PF1403T  | 1.1-1.6 ADA UNIV BOWL | ○ White ○ Biscuit |
| PF5112HE | HET Tank only 12" RI for 1400 series | ○ White ○ Biscuit |
| PF5112NHEWH | HET Tank only 12" RI for 1400 series | ○ White |
| PF5112BHEWH | HET Low Profile Tank only 12" RI for 1400 series | ○ White |
| PF5110HE | HET Tank only 10" RI for 1400 series | ○ White ○ Biscuit |
| PF5114HEWH | HET Tank only 14" RI for 1400 series | ○ White |
| PF5112RHEWH | HET Right Hand Tank only | ○ White |
| PF5112UHEWH | HET Lined Tank only 12" RI for 1400 series | ○ White |
| PF5112LHEWH | Tank with Locking Lid | ○ White |

* = complies with CSA B651

wheelchair symbol = complies with ADA & CSA B651



High-Efficiency Two Piece Toilet




Product Features


The combination toilet shall be made of vitreous china. Toilet shall be 1.28 GPF (4.8 lpf). Toilet shall have 2" (5.1cm) fully glazed trapway. Toilet shall include color match trip lever. Toilet shall be less seat and supply. Toilet shall be ADA compliant (PF1403T) with 17" high bowl.

Warranty and Codes:

This product comes complete with installation, operating, care and maintenance instructions. All PROFLO fixtures carry a limited lifetime warranty on the vitreous china and a 5-year limited warranty on the parts and fittings. This product meets or exceeds ASME/ANSI A112.19.2M. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed product to fill any order unless we agree in writing to do otherwise.



| | A | B | C | D | E | F | G |
|---------------------|---------|---------|---------|---------|--------|-----|---------|
| PF5114HE / PF1400T | 30-1/2" | 16-1/2" | 15" | 29-3/4" | 9-3/4" | 14" | 15-3/4" |
| PF5114HE / PF1401T | 32-1/2" | 18-1/2" | 15" | 29-3/4" | 9-3/4" | 14" | 15-3/4" |
| PF5114HE / PF1402T | 32-1/2" | 18-1/2" | 16-1/4" | 31" | 9-3/4" | 14" | 15-3/4" |
| PF5114HE / PF1403T | 32-1/2" | 18-1/2" | 17" | 31-3/4" | 9-3/4" | 14" | 15-3/4" |
| PF5110HE / PF1400T | 26-1/2" | 16-1/2" | 15" | 29-3/4" | 6-1/4" | 10" | 17-1/2" |
| PF5110HE / PF1401T | 28-1/2" | 18-1/2" | 15" | 29-3/4" | 6-1/4" | 10" | 17-1/2" |
| PF5110HE / PF1402T | 28-1/2" | 18-1/2" | 16-1/4" | 31" | 6-1/4" | 10" | 17-1/2" |
| PF5110HE / PF1403T | 28-1/2" | 18-1/2" | 17" | 31-3/4" | 6-1/4" | 10" | 17-1/2" |
| PF5112HE / PF1400T | 28-1/2" | 16-1/2" | 15" | 29-3/4" | 8-1/2" | 12" | 15-3/4" |
| PF5112HE / PF1401T | 30-1/2" | 18-1/2" | 15" | 29-3/4" | 8-1/2" | 12" | 15-3/4" |
| PF5112HE / PF1402T | 30-1/2" | 18-1/2" | 16-1/4" | 31" | 8-1/2" | 12" | 15-3/4" |
| PF5112HE / PF1403T | 30-1/2" | 18-1/2" | 17" | 31-3/4" | 8-1/2" | 12" | 15-3/4" |
| PF5112BHE / PF1400T | 28-1/2" | 16-1/2" | 15" | 26-3/4" | 8-1/2" | 12" | 15-3/4" |
| PF5112BHE / PF1401T | 30-1/2" | 18-1/2" | 15" | 26-3/4" | 8-1/2" | 12" | 15-3/4" |
| PF5112BHE / PF1402T | 30-1/2" | 18-1/2" | 16-1/4" | 28" | 8-1/2" | 12" | 15-3/4" |
| PF5112BHE / PF1403T | 30-1/2" | 18-1/2" | 17" | 28-5/8" | 8-1/2" | 12" | 15-3/4" |



Footprint

| | RF | EL | CH EL | ADA |
|---|---------|---------|---------|---------|
| | PF1400T | PF1401T | PF1402T | PF1403T |
| H | 18-1/2" | 18-1/2" | 18-1/2" | 18-1/2" |
| I | 6" | 6" | 6" | 6" |
| J | 6-1/8" | 6-1/2" | 6-1/2" | 6-1/2" |
| K | 9" | 9" | 9" | 9" |

