

GRUNDFOS V

1/4

GRUNDFOS X

Company name: -

Created by: Phone: Fax:

Date:

-

-

-

Date				
Position	Count	Description		Unit price
		Port-to-port length:	6 1/2 in	
		Electrical data:		
		Number of poles:	2	
		Power input in speed 1:	265 W	
		Power input in speed 2: Max. power input:	335 W 370 W	
		Rated power - P2:	0.335 HP	
		Main frequency:	60 Hz	
		Rated voltage:	1 x 115 V	
		Current in speed 1:	2.5 A	
		Current in speed 2:	3.1 A	
		Current in speed 3:	3.5 A	
		Capacitor size - run:	40 µF/180 V	
		Insulation class (IEC 85):	Н	
		Others:		
		Gross weight:	16.8 lb	





